1445716-2 ✔ ACTIVE


AMP Power Series - 75

TE Internal #: 1445716-2

AMP Power Series - 75, Rectangular Power Connectors, Connector Assembly, Plug / Receptacle, Wire-to-Wire, 1 Position, Wire & Cable, UL 94V-0

View on TE.com >

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors




Rectangular Power Connector Type: **Connector Assembly**

Connector & Housing Type: **Plug, Receptacle**

Connector System: **Wire-to-Wire**

Number of Positions: **1**

Sealable: **No**

Features

Product Type Features

Assembly Requirement	Unassembled Kit
Rectangular Power Connector Type	Connector Assembly
Connector & Housing Type	Plug, Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VDC

Contact Features

Contact Current Rating (Max)	75 A
Contact Retention Within Housing	Without

Contact Type	Pin, Socket
Wire Contact Termination Area Plating Material	Silver
Contact Mating Area Plating Material	Silver
Contact Mating Area Plating Material Thickness	1.27 µm[50 µin]

Termination Features

Termination Method to Wire & Cable	Crimp
Wire Type	Stranded

Mechanical Attachment

Mating Alignment	Without
Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	Without

Housing Features

Housing Color	Black
Housing Material	Polycarbonate

Dimensions

Wire Size	25656 – 27629 CMA
Height	17.15 mm[.675 in]
Length	48 mm[1.89 in]
Width	17.15 mm[.675 in]

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]

Operation/Application

Circuit Application	Power

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire
UL Rating	Recognized
Agency/Standard Number	E28476
Agency/Standard	UL

Packaging Features

Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 647877-1
SERIES 50 & 75 CONTACT,6 AWG



TE Part # 1445715-2
75A HSG SUBASY BLACK

Also in the Series | AMP Power Series - 75



Rectangular Power Connectors(18)

Customers Also Bought



TE Part #T4171010004-001
M12 Panel Mount Wire



TE Part #1-66099-5
TYPE III CONTACTS LP



TE Part #1-1879450-5
Wirewound Resistor: Mineral, 2.5 Kw




TE Part #1-1879417-8
CPF 0603 910K 0.1% 25PPM 1K RL



TE Part #1-1624112-9
3650 0402 3.6nH 5% 2K RL



TE Part #1-1718644-1
MCON, CONNECTOR HOUSING



TE Part #1-57013-3
Madison Spec 100-4136 Rev. 3



TE Part #1393248-5
W33-S1N1Q-10=W33



TE Part #1-1546311-0
10P.563" DR BARRIER,W/WASHER

Documents

Product Drawings

KIT 6AWG BLACK

English

CAD Files

Customer View Model

ENG_CVM_1445716-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_1445716-2_A.3d_stp.zip

English

Customer View Model

ENG_CVM_1445716-2_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

AMP Power Series 50 and 75 Connectors

English

Engineering Report

English