



Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Tab**
Wire Size: **.51 – 1.65 mm²**
Quick Disconnect Mating Tab Width: **2.8 mm [.11 in]**
Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Pre-Tin

Contact Features

Terminal Type	Tab
Terminal & Splice Type	Tab



Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	1.4 – 2.3 mm[.055 – .09 in]
Overall Length	21.4 mm[.842 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	.51 – 1.65 mm²
Quick Disconnect Mating Tab Width	2.8 mm[.11 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	6000
Quick Disconnect Packaging Method	Strip/Reel

Other

Comment	According to DIN 46343, Part 1
---------	--------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1579007-4
EXTRACTION TOOL



TE Part # 4-1579007-3
EXTRACTION TOOL KIT



TE Part # 175048-1
FF 187 TAB 2-3MM2 PTBR



TE Part # 160719-3
FASTIN FASTON (FF) TAB 20/16 AWG BR



TE Part # 2-2150319-2
OCEAN_2.0_Applicator-E-080F110OV-A



TE Part # 2150319-2
OCEAN_2.0_Applicator-E-080F110OV-A



TE Part # 7-2150319-2
OCEAN_2.0_Applicator-E-080F110OV-A



TE Part # 7-2150319-7
OCEAN_2.0_SPARE_PART_KIT-080F110OV



TE Part # 539743-2
DIE F2.8FF TAB

Also in the Series | FASTIN-FASTON 110



Automotive Housings(1)



Automotive Terminals(4)



Crimp Terminal Housings(35)



Insertion & Extraction Tools(3)



Quick Disconnects(84)

Customers Also Bought



TE Part #1-2176341-1
CRGCQ 0805 68R 1%



TE Part #1-2176412-6
5W XSM M/OX 5% 22R



TE Part #1-2176412-8
5W XSM M/OX 5% 27R



TE Part #1-962841-2
TIMER, RECEPTACLE AND TAB



TE Part #144935-1
MQS, CONNECTOR HOUSING



TE Part #1379096-1
COV+LEV MQS 12W 90DEG BRO



TE Part #144936-1
LOCKING DEVICE MQS



TE Part #1534027-1
MQS VERRIEGLUNG F2P



TE Part #1-2176264-4
RN 0805 698K 0.1% 10PPM 1K RL

Documents



Product Drawings

FF 110 TAB 0.5-1.0MM2 PTPPB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160887-4_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_160887-4_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_160887-4_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

Product Compliance

English

Product Compliance

English