



PIDG

TE Internal #: 152872
PIDG, Ring Terminals & Spade Terminals, Ring Tongue, 14 – 12AWG Wire Size, 1.65 – 3.45mm² Wire Size, 3260 – 6800CMA Wire Size, M5

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**
Wire Size: **3260 – 6800 CMA**
Ring & Spade Stud Size: **M5**

Features

Product Type Features

Shape Description	RING-041
Ring & Spade Stud Size	M5
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	No
Insulation Sleeve Color	White
Weight per Piece	1.078 g
Stripe Color	White
Ring & Spade Plating Material	Tin

Contact Features

--	--



Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	3260 – 6800 CMA
Stud Diameter	5 mm[.197 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	22.02 mm[.865 in]
Ring & Spade Wire Insulation Diameter (Max)	3.18 mm[.125 in]
Ring & Spade Wire Insulation Diameter	2.03 – 3.18 mm[.08 – .125 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	500
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 576782
HHHT PIDG PEEK STRATO 14 ASSY

TE Part # 576783
HHHT PIDG PEEK STRATO 12 ASSY

Also in the Series | PIDG

Compression Connectors(17)

Crimp Terminal Housings(1)

Crimp Wire Pins, Tabs & Ferrules(41)

Knife Disconnects(11)

PCB Terminals(9)

Portable Crimp Tools(2)

Quick Disconnects(53)

Ring Terminals & Spade Terminals(862)



Special Purpose Terminals(1)



Splices(48)

Customers Also Bought



TE Part #151439
PIDG 22 RING #6



TE Part #152871
14-12 PIDG R/T 1/4 STUD WHITE



TE Part #152873
14-12 PIDG NYLON RT NO 8 WHITE



TE Part #152884
18-16 PIDG RT NO 6 STUD ORANGE



TE Part #151441
TERMINAL PIDG RING TONGUE 22 AWG BLACK



TE Part #152874
14-12 PIDG R/T NO6STUD WHITE




TE Part #F02422-000
HX-SCE LOW FIRE HAZARD SLEEVES



TE Part #151440
PIDG 22 RING #8



TE Part #152892
SIZE 20 PIDG R/T NO.10 NYLON



TE Part #1230193001
99M0111-20-1

Documents

Product Drawings

14-12 PIDG NYLON RT NO 10WHITE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_152872_J.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_152872_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_152872_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English