




Connectors > Modular Jacks & Plugs > RJ45 Connectors



Modular Jack & Plug Interface Type: **RJ45**

Port Configuration: **Multiple Ports**

Port Matrix Configuration: **1 x 2**

Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Features

Product Type Features

Connectors & Connector Components Type	Connector
Connector Product Type	Connector Assembly
Modular Jack & Plug Interface Type	RJ45
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Modular Connector Style	Jack
Grounding Options	None
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Port Configuration	Multiple Ports
Port Matrix Configuration	1 x 2
Connector Contact Density	Standard
Multiple Port Configuration	Ganged
Status Indicator Type	None
Number of Positions	8
Number of Loaded Positions	8



PCB Mount Orientation	Right Angle
Body Features	
Modular Jack Latch Orientation	Inverted - Latch Up
Connector Profile	Standard
Contact Features	
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	1.5 A
Contact Mating Area Plating Material	Gold
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material Thickness	1.27 µm[50 µin]
Termination Features	
Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post & Tail Length	2.54 mm[.1 in]
Mechanical Attachment	
Panel Mount Feature	Without
Connector Mounting Type	Board Mount
Housing Features	
Mating Entry Location	Side
Centerline (Pitch)	1.02 mm[.04 in]
Housing Color	Black
Housing Material	High Temperature Thermoplastic
Dimensions	
Connector Height	12.83 mm[.505 in]
Usage Conditions	
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
Operation/Application	
Shielded	No
Circuit Application	Signal
Industry Standards	
UL Flammability Rating	UL 94V-0



Performance Category

Cat 5

Packaging Features

Packaging Quantity	72
Packaging Method	Box & Tray, Tray

Other

Comment	Recommended applications: Fast Ethernet, 10Base-T Ethernet, and 10/100 Base-T Ethernet (Cat 5 on two pair 1/2, 3/6).
---------	--

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 188729-1
8P.COVER/SOLD.STOP

Customers Also Bought



TE Part #1775470-2
AMP HPI 2.0MM HEADERS



TE Part #1734709-2
AMP HPI 1.0MM HEADERS



TE Part #2-1393222-0
V23061A1005A302=MINISTARKSTROM



TE Part #1437565-3
FSM101=12MM FSM TYPE WITH RAIS



TE Part #1879022-1
SMD Power Resistor: 7 Watt, 200-2M Ohm




TE Part #1-2301994-1
RJ45 JACK INT.MAG. 1GB LED 1X1 INV (LOW)



TE Part #1825966-1
FSMCH=3.5 X 6.0 X 4.3 TACT SWITCH, HT



TE Part #9-1879061-8
CPF0402 110K 0.1% 25PPM 5K RL



TE Part #1393564-6
C42121A 40C 14=HALTERUNG



TE Part #1-179019-1
LOW & MEDIUM POWER HEADER

Documents

Product Drawings

INV MJ ASSY,1X2

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5406526-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_5406526-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5406526-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

[MD_5406526-1_03052014823_dmtec](#)

English

[MD_5406526-1_03052014823_dmtec](#)

English