



TE Internal #: 2-406549-5

RJ45 Connectors, RJ45, Single Port, Port Matrix Configuration 1 x 1, RJ Type Jacks & Plugs, Standard Connector Contact Density, Jack, Shielded, Cat 5

[View on TE.com >](#)

Connectors > Modular Jacks & Plugs > RJ45 Connectors



Modular Jack & Plug Interface Type: **RJ45**

Port Configuration: **Single Port**

Port Matrix Configuration: **1 x 1**

Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Features

Product Type Features

|                                        |                       |
|----------------------------------------|-----------------------|
| Connectors & Connector Components Type | Connector             |
| Connector Product Type                 | Connector Assembly    |
| Modular Jack & Plug Interface Type     | RJ45                  |
| Modular Jacks & Plugs Products         | RJ Type Jacks & Plugs |
| Modular Connector Style                | Jack                  |
| Grounding Options                      | PCB and Panel Ground  |
| Connector & Contact Terminates To      | Printed Circuit Board |

Configuration Features

|                             |                   |
|-----------------------------|-------------------|
| Panel Ground Location       | Top and Side, Top |
| Number of PCB Ground Tabs   | 2                 |
| Number of Panel Ground Tabs | 2                 |
| Port Configuration          | Single Port       |
| Port Matrix Configuration   | 1 x 1             |
| Connector Contact Density   | Standard          |
| Status Indicator Type       | LED               |



|                            |             |
|----------------------------|-------------|
| Number of Positions        | 8           |
| Number of Loaded Positions | 8           |
| PCB Mount Orientation      | Right Angle |

Body Features

|                                |                     |
|--------------------------------|---------------------|
| PCB Ground Tab Location        | -3.43 mm[-.135 in]  |
| Shield Plating Material        | Tin                 |
| Shield Material                | Copper Alloy        |
| Modular Jack Latch Orientation | Inverted - Latch Up |
| Connector Profile              | Standard            |
| LED Color (Top Left)           | Green               |
| LED Color (Top Right)          | Green               |

Contact Features

|                                                |                 |
|------------------------------------------------|-----------------|
| PCB Termination Area Plating Finish            | Matte           |
| Contact Underplating Material                  | Nickel          |
| PCB Contact Termination Area Plating Material  | Tin             |
| Contact Current Rating (Max)                   | .2 A, 1.5 A     |
| Contact Mating Area Plating Material           | Gold            |
| Contact Base Material                          | Phosphor Bronze |
| Contact Mating Area Plating Material Thickness | .38 µm[15 µin]  |

Termination Features

|                                             |                       |
|---------------------------------------------|-----------------------|
| Termination Method to Printed Circuit Board | Through Hole - Solder |
| Termination Post & Tail Length              | 2.54 mm[.1 in]        |

Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| Panel Mount Feature     | Without     |
| Connector Mounting Type | Panel Mount |

Housing Features

|                       |                                |
|-----------------------|--------------------------------|
| Mating Entry Location | Side                           |
| Centerline (Pitch)    | 1.02 mm[.04 in]                |
| Housing Color         | Black                          |
| Housing Material      | High Temperature Thermoplastic |

Dimensions

|                             |                  |
|-----------------------------|------------------|
| PCB Thickness (Recommended) | 1.57 mm[.062 in] |
|-----------------------------|------------------|



|                  |                   |
|------------------|-------------------|
| Connector Height | 13.34 mm[.525 in] |
|------------------|-------------------|

Usage Conditions

|                             |                                         |
|-----------------------------|-----------------------------------------|
| Operating Temperature Range | -40 – 85 °C[-40 – 185 °F][-40 – 185 °F] |
|-----------------------------|-----------------------------------------|

Operation/Application

|                     |        |
|---------------------|--------|
| Shielded            | Yes    |
| Circuit Application | Signal |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
| Performance Category   | Cat 5    |

Packaging Features

|                    |                  |
|--------------------|------------------|
| Packaging Quantity | 63               |
| Packaging Method   | Box & Tray, Tray |

Other

|         |                                                                                                                      |
|---------|----------------------------------------------------------------------------------------------------------------------|
| Comment | Recommended applications: Fast Ethernet, 10Base-T Ethernet, and 10/100 Base-T Ethernet (Cat 5 on two pair 1/2, 3/6). |
|---------|----------------------------------------------------------------------------------------------------------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                  |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part






numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 188729-1  
8P.COVER/SOLD.STOP

Customers Also Bought



TE Part #1-487526-5  
2.54mm FFC Connectors Receptacle Housing



TE Part #2-487545-7  
FFC Receptacle Housing: 1.27mm



TE Part #1888617-1  
Cage Assy, QSFP, Through Bezel



TE Part #2007262-1  
SFP+ 1x2 Cage Assembly, Light




TE Part #2-1926739-5  
AssyMinipak HdI25s10pRARecptSc




TE Part #1489948-2  
XFP HEAT SINK CLIP, PLATED



TE Part #1551920-2  
zQSFP+ connector assembly



TE Part #2-327958-1  
PIDG RECTANGULAR TONGUE TERMINALS



TE Part #2-690471-9  
COMB ANVIL



TE Part #925370-5  
MOD IV REC HSG 2X5P.

Documents

Product Drawings



IMJ,1X1,PNL GRD,LED(G/G), SN

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-406549-5\_R1.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-406549-5\_R1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-406549-5\_R1.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Product Environmental Compliance

MD\_2-406549-5\_12042015859\_dmtec

English

MD\_2-406549-5\_12042015859\_dmtec

English

Agency Approvals

UL Report

English