



Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Tab**

Wire Size: **.32 – .82 mm²**

Quick Disconnect Mating Tab Width: **6.35 mm [.25 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Silver

Contact Features

Terminal Type	Tab
Terminal & Splice Type	Tab



Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

	.055 in
Mating Retention Type	Locking Lance
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.2 – 3.3 mm[.087 – .126 in]
Overall Length	28 mm[1.1 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm ²
Quick Disconnect Mating Tab Width	6.35 mm[.25 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
------------------------	-------------

Packaging Features

Packaging Quantity	3500
Quick Disconnect Packaging Method	Strip/Reel

Other

Comment	"According to DIN, except Wire Size Range", Tab for crimping Tab Housing Part No. 927203., With locking hole.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



Halogen Content	Does not contain REACH SVHC
Solder Process Capability	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 91514-1
CCII FASTON 250 REC 22-18 ASSY

TE Part # 2-2150037-2
OCEAN_2.0_APPLICATOR-E-090F140F

TE Part # 2150037-2
OCEAN_2.0_APPLICATOR-E-090F140F

TE Part # 7-2150037-2
OCEAN_2.0_APPLICATOR-E-090F140F

TE Part # 7-2150037-7
OCEAN_2.0_SPARE_PART_KIT-090F140F

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(216)



Insertion & Extraction Tools(2)



PCB Terminals(2)




Quick Disconnects(258)

Customers Also Bought




TE Part #1735446-3
AMP HPI 2.0MM HEADERS



TE Part #1971032-3
3P HEADER ASSEMBLY FOR GIC 2.0 EV



TE Part #1-2834074-2
SLIMSEAL MINIATURE PLUGS



TE Part #140791-2
WIRE TERMINAL 18-14 AWG 0.24 X .394 TPBR



TE Part #1-2834067-2
SOCKET CONTACT,MINIATURE WATERPROOF CONN




TE Part #104920-2
03 MTE RCPT HSG SR LATCH .100



TE Part #1633963-2
CRIMPER, INSULATION F PREMIUM



TE Part #CV00476001
QSZH-125-NR4-45MM



TE Part #1703058-1
7POS.SPECIAL POSITIVE MATE TAB HSG.

Documents

Product Drawings

FF 250 TAB 22-18AWG BR SILVER PLATED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160691-5_Z.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_160691-5_Z.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_160691-5_Z.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English