




Connectors > Automotive Connectors > Connector Accessories > Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover - Cable Exit**

Cable Exit Angle: **180° (In-Line)**

Strain Relief: **Without**

Primary Product Color: **Natural**

Primary Product Material: **PBT GF**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover - Cable Exit
Connector System	Wire-to-Board, Wire-to-Device

Configuration Features

Number of Positions	18
---------------------	----

Body Features

Cable Exit Angle	180° (In-Line)
Primary Product Color	Natural
Primary Product Material	PBT GF

Mechanical Attachment

Strain Relief	Without
---------------	---------

Dimensions

Cable Bundle Diameter	4.3 mm[.169 in]
-----------------------	-----------------

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Industry Standards



UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	1000
Packaging Method	Carton

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-M8793-CH8172
MQS, CONNECTOR HOUSING

TE Part # CAT-SIGH262
SIGNAL HEADER

Also in the Series

MQS

Automotive Connector Caps & Covers
(133)

Automotive Connector EMC Shielding
(2)

Automotive Connector Locks & Position Assurance(29)

Automotive Headers(207)

Automotive Housings(498)

Automotive Seals & Cavity Plugs(26)

Automotive Terminals(98)

Data Connectivity Headers(1)

Insertion & Extraction Tools(42)

Other Automotive Connector Accessories(13)

Customers Also Bought

TE Part #WP-4P
DEUTSCH DTP WEDGELOCKS

TE Part #1060-12-0222
DEUTSCH STAMPED & FORMED CONTACTS

TE Part #1355348-1
MQS, CONNECTOR HOUSING

TE Part #1393366-1
GET .64 CONNECTOR SYSTEM, RECEPT AND TAB



TE Part #1-1419158-8
GET .64 CONNECTOR SYSTEM,
CONNECTOR HSG

TE Part #1379100-2
COV+LEV MQS 18W 0DEG WHI

TE Part #144936-1
LOCKING DEVICE MQS

TE Part #1544664-1
WIRE SEAL 8NG1

TE Part #1326110-1
46P PLUG ASSY,EBC440,RIGHT H,
1SLOT,W/2.8

Documents

Product Drawings
MQS COVER 18POS

English

CAD Files
3D PDF

English

Customer View Model
ENG_CVM_2-1355350-1_A1.2d_dxf.zip

English

Customer View Model
ENG_CVM_2-1355350-1_A1.3d_igs.zip

English

Customer View Model
ENG_CVM_2-1355350-1_A1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Micro Quardlok System Female Connectors

English

Product Specification

English