




Connectors > Modular Jacks & Plugs > RJ14 Connectors > RJ14 Connectors



Port Configuration: **Single Port**
Port Matrix Configuration: **1 x 1**
Connector Profile: **Low**
Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**
Connector Contact Density: **Standard**

[All RJ14 Connectors \(5\)](#)

Features

Product Type Features

Connectors & Connector Components Type	Connector
Modular Jack & Plug Interface Type	RJ14
Grounding Options	None
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Modular Connector Style	Jack
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Status Indicator Type	None
Port Configuration	Single Port
Port Matrix Configuration	1 x 1
Connector Contact Density	Standard
PCB Mount Orientation	Vertical



Number of Positions	6
Number of Loaded Positions	4

Body Features

Connector Profile	Low
Modular Jack Latch Orientation	Standard - Latch Down

Contact Features

Contact Mating Area Plating Material Thickness	1.27 µm
Contact Underplating Material	Nickel
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	.2 A, 1.5 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post & Tail Length	3.18 mm[.125 in]

Mechanical Attachment

Panel Mount Feature	With
Connector Mounting Type	Board Mount

Housing Features

Mating Entry Location	Top
Housing Color	Black
Housing Material	PBT Polyester
Centerline (Pitch)	1.02 mm[.04 in]

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	16.5 mm[.65 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
-----------------------------	---

Operation/Application

Shielded	No
Circuit Application	Signal



Industry Standards

Performance Category	Cat 3
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Box & Tray, Package, Tray
Packaging Quantity	2816

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




Also in the Series | CGS TE



Also in the Series | OEG Miniature Relay PCF





Power Relays(4)



RJ14 Connectors(3)



RJ22 Connectors(3)



RJ25 Connectors(10)



RJ45 Connectors(70)



Wire-to-Board Connector Contacts(1)

Customers Also Bought



TE Part #2-5747706-0
D-Sub Receptacle Assembly: Vertical, Shell Size 1, 2.74mm



TE Part #1445390-3
MINI CPC



TE Part #1-640445-1
11P MTA156 HDR ASSY FL/STR SN



TE Part #2-1393225-1
RY611024



TE Part #8-1437653-0
6PCV-16-006=6PCV ASSEMBLY




TE Part #1-640383-1
11P MTA156 HDR ASSY STR SQ SN




TE Part #207602-1
METRIMATE,STR REL KIT,12P



TE Part #1-770969-0
06P MINI UMNL R/A HDR ASSY SN



TE Part #102548-1
MOD IV RECP PLTD 15 SEL



TE Part #1437537-5
DIP Socket: Standard, Screw Machine, Open, Gold

Documents



Product Drawings

MJ,TE,6P/4C,BULK PAC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5520425-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5520425-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5520425-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82066 - Modular Jacks and MRJ21 Product catalog - Single Port Modular Jacks section

English

1-1773464-9_MODULAR_JACKS_SINGLE_PORT_PCB_MOUNT

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English