1986711-5 ✔ ACTIVE



Buchanan

TE Internal #: 1986711-5

PCB Terminal Blocks, Header, Wire-to-Board, 5 Position, 5mm [.197in] Centerline, 2 Row, Side Wire Entry Angle, 30 – 12AWG Wire Size

View on TE.com >

Connectors > Terminal Blocks & Strips > PCB Terminal Blocks




Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **5**

Centerline (Pitch): **5 mm [.197 in]**

Number of Rows: **2**

Features

Product Type Features

Wire Protection	With
Block Type	Straight
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Threaded Flange	Without
Number of Positions	5
Number of Rows	2
Wire Entry Angle	Side

Electrical Characteristics

Current Rating (Max)	16 A
Voltage Rating	300 VAC

Body Features

Interlock	Without
Lever Color	White

Contact Features

Contact Mating Area Plating Material	Tin
Contact Mount	Through Hole
Pin Length	3.5 mm[.138 in]
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	16 A

Mechanical Attachment

Screwless Terminal Block	Yes
Mounting Angle	Straight
Screw Flange	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Green
Housing Material	Polyamide
Centerline (Pitch)	5 mm[.197 in]

Dimensions

PCB Tail Length	3.5 mm[.138 in]
Wire Size	.05 – 3 mm^2

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Circuit Application	Power & Signal

Packaging Features

Packaging Quantity	150

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 1986712-5
SCREWLESS, SW,5P,5.08 PCB



TE Part # 1986774-5
SCREWLESS, SW,5P,5.0 PCB, Low Amp

Customers Also Bought



TE Part #2-1879464-2
Thick Film Resistor: Current Sense



TE Part #T4171320008-001
M12 Panel Mount Wire



TE Part #170364-1
MINI UNIVERSAL M-N-L PIN LP



TE Part #1986711-2
SCREWLESS, SW,2P,5.0 PCB



TE Part #1986711-3
SCREWLESS, SW,3P,5.0 PCB




TE Part #1986711-4
SCREWLESS, SW,4P,5.0 PCB



TE Part #1624023-2
SC30-10-2519-10 3.3UH AMMO 1000



TE Part #160075
SOLIS 4 R M10



TE Part #1586863-4
4P VAL-U-LOK R/A HDR GW



TE Part #1622682-1
LR2 1% 12K

Documents

Product Drawings

SCREWLESS, SW,5P,5.0 PCB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1986711-5_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1986711-5_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1986711-5_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Agency Approvals

VDE Certificate

English