



OEG Miniature Relay PCF

TE Internal #: 1888653-5

OEG Miniature Relay PCF, RJ45 Connectors, RJ45, Multiple Ports, Port Matrix Configuration 2 x 1, RJ Type Jacks & Plugs

[View on TE.com >](#)

Connectors > Modular Jacks & Plugs > RJ45 Connectors



Modular Jack & Plug Interface Type: **RJ45**

Port Configuration: **Multiple Ports**

Port Matrix Configuration: **2 x 1**

Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Features

Product Type Features

Connectors & Connector Components Type	Connector
Connector Product Type	Connector Assembly
Ground Component Type	Grounding Clips
Modular Jack & Plug Interface Type	RJ45
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Modular Connector Style	Jack
Grounding Options	PCB and Panel Ground
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Panel Ground Location	Sides
Number of Grounding Clips	1
Number of PCB Ground Tabs	4
Number of Panel Ground Tabs	12
Wiring Pattern	Cat 5e
Port Configuration	Multiple Ports



Port Matrix Configuration	2 x 1
Connector Contact Density	Standard
Multiple Port Configuration	Stacked
Status Indicator Type	LED
Number of Positions	8
Number of Loaded Positions	8
PCB Mount Orientation	Right Angle

Signal Characteristics

Data Rate	1000 Mb/s
-----------	-----------

Body Features

Insulator Material	Thermoplastic Polyester
Shield Plating Finish	Tin
Grounding Tab Plating Material	Tin over Copper
Shield Plating Material	Tin over Copper
Shield Material	Copper Alloy
Modular Jack Latch Orientation	Standard - Latch Down
Connector Profile	Offset - Overhangs PCB
LED Color (Bottom Left)	None
LED Color (Bottom Right)	None
LED Color (Top Left)	Green
LED Color (Top Right)	Yellow

Contact Features

PCB Termination Area Plating Finish	Matte
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	1.5 A
Contact Mating Area Plating Material	Gold
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material Thickness	.38 μ m[15 μ in]

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Press-Fit
Termination Post & Tail Length	4.14 mm[.163 in]



Mechanical Attachment

Panel Mount Feature	Without
PCB Mount Retention Type	SMT Hold Down - Press-Fit
Mating Retention Type	Latch
Connector Mounting Type	Board Mount, Panel Mount

Housing Features

Mating Entry Location	Side
Centerline (Pitch)	1.02 mm[.04 in]
Housing Color	Black
Housing Material	PBT GF

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Height	3.27 mm[.129 in]

Usage Conditions

Housing Material Temperature	High
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]

Operation/Application

Shielded	Yes
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
Performance Category	Cat 5e

Packaging Features

Packaging Quantity	45
Packaging Method	Tray

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2021
 (211)
 Candidate List Declared Against: JAN 2021
 (211)
 Does not contain REACH SVHC


Halogen Content Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 188729-1
8P.COVER/SOLD.STOP




TE Part # 1521003-2
CAT 5E CABLE ASSY, 8 POS RJ45

Also in the Series | OEG Miniature Relay PCF




Board-to-Board Headers & Receptacles(4)




Combo Jacks(2)



IDC D-Sub Connectors(1)



Mini PCI Express & mSATA(1)



Power Relays(4)



RJ14 Connectors(3)



RJ22 Connectors(3)



RJ25 Connectors(10)



RJ45 Connectors(70)




Wire-to-Board Connector Contacts(1)

Customers Also Bought




TE Part #1489951-1
XFP Cage Assemblies and Kits



TE Part #1367500-1
XFP Heat Sink




TE Part #9-1469373-9
ATCA GUIDE MODULE RA FEMALE



TE Part #120943-1
UPM R/A REC HC 3P Power Connector




TE Part #1055688-1
2367 5001 54, VERT PLUG



TE Part #1761014-3
SFP 1X2 CAGE ASSY, PRESS FIT



TE Part #1489948-2
XFP HEAT SINK CLIP, PLATED



TE Part #1-338088-6
8/8 INV.MOD.JACK



TE Part #1551920-2
zQSFP+ connector assembly



TE Part #1551891-1
Cage Assy, Behind Bezel, QSFP28

Documents



Product Drawings

2X1 OFFSET ST/JK WITH LEDS

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1888653-5_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1888653-5_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1888653-5_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Offset Stacked Modular Jack with LED_s, Category 5

English

Product Environmental Compliance

MD_1888653-5_021920181147_dmtec

English

MD_1888653-5_021920181147_dmtec

English

Agency Approvals

UL Report

English