

Multilock Connector System


TE Internal #: 175977-2

Multilock Connector System, Automotive Headers, 36 Position, 2.5 mm [.098in] Centerline, Vertical, 2 Row, Black, Through Hole - Solder, Tin (Sn)

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Headers > SIGNAL HEADER



Number of Positions: 36
Centerline (Pitch): 2.5 mm [.098 in]
Sealable: No
PCB Mount Orientation: Vertical
Number of Rows: 2

[All SIGNAL HEADER \(423\)](#)

Features

Product Type Features

Hybrid Header	No
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Sections	2
Number of Signal Positions	36
Number of Positions	36
PCB Mount Orientation	Vertical
Number of Rows	2

Electrical Characteristics

Voltage Rating (Max)	12 VDC
Nominal Voltage Architecture	12 V
Operating Voltage	12 VDC

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

--	--



Mating Tab Width	1 mm[.039 in]
Mating Tab Thickness	.64 mm[.025 in]
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Locking Interface	With
Mounting Holes	With
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without

Housing Features

Centerline (Pitch)	2.5 mm[.098 in]
--------------------	-----------------

Dimensions

Profile Height from PCB	20.7 mm[.815 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Product Width	61 mm[2.402 in]
Product Length	16.9 mm[.665 in]

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C[149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Shielded	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Type	Tube
Packaging Quantity	100

Other

--	--



Interface Number	175967
------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-M9194-CH8172
MULTILOCK, CONNECTOR HOUSING



TE Part # 175967-5
040 MLC-2 PLUG HSG ASSY 20P


Also in the Series | Multilock Connector System



Automotive Connector Caps & Covers
(16)



Automotive Connector EMC Shielding
(1)



Automotive Connector Locks &
Position Assurance(2)



Automotive Headers(138)



Automotive Housings(576)



Automotive Seals & Cavity Plugs(2)



Automotive Terminals(142)



Insertion & Extraction Tools(6)



Other Automotive Connector
Accessories(9)

Customers Also Bought



TE Part #1-207441-0
METRIMATE PIN HDR ASY,9P LF



TE Part #1565357-6
ON TAPING(EMBOSS) 0.5MM PITCH



TE Part #1123339-1
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #1376111-2
SIGNAL HEADER



TE Part #DRC23-40PB-N012
DEUTSCH DRC HEADERS



TE Part #1473140-1
SQUIB 11DIA MK-2 LOCKING BUTTO



TE Part #1612119-1
11DIA SQUIB SLIM MK-2 LOCKING



TE Part #1376689-1
11DIA SQUIB SLIM LOCK BUTTON

Documents



Product Drawings

040 MLC CAP ASS'Y V 36P

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_175977-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_175977-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_175977-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

Japanese

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Customer Manual (non U.S.)

Japanese

.040 Series, Multilock I/O Connector, Mark II

Japanese

Customer Manual (non U.S.)

Japanese

.040 Series Multilock I/O Connector Mark II

Japanese