




Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Marking Accessories



Marking Product Type: **Marker Card**

Pre-Printed Mark Details: **0 -> 9 (x10)**

Primary Product Color: **White**

Product Orientation: **Horizontal**

UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

|                      |             |
|----------------------|-------------|
| Marking Product Type | Marker Card |
|----------------------|-------------|

Configuration Features

|                          |              |
|--------------------------|--------------|
| Pre-Printed Mark Details | 0 -> 9 (x10) |
|--------------------------|--------------|

Body Features

|                       |            |
|-----------------------|------------|
| Primary Product Color | White      |
| Product Orientation   | Horizontal |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-2 |
|------------------------|----------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per                                                                                      |



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1SNA115116R0700  
M4/6

Customers Also Bought

TE Part #1-222246-0  
CONTACT,PLUG,COML BNC PLATED

TE Part #282928-1  
CAVITY IDENTIF.LABEL 10P.5/5,0

TE Part #641191-4  
Nylon Gold Plated Receptacle: 2.54 mm, No Mating Alignment, MTA 100

TE Part #1-644020-4  
Nylon Gold Plated Receptacle: 2.54 mm, With Mating Alignment, MTA 100

TE Part #YDTS20F21-35PN0000  
D38999: Square Flange, 21-35 insert

TE Part #293722-1  
NECTOR M PIN HSG FREE HANGING 7P CODE A

TE Part #227079-9  
COMM. BNC-PLUG

TE Part #2836167-1  
OC-AT-S-FM-045F-055-1015



Documents

Product Drawings

RC65 0->9 (X10) HORIZONTAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1SNA232001R2500\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1SNA232001R2500\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1SNA232001R2500\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RC65 0->9 (x10) Horizontal

English

ENTRELEC Terminal Block - Master Catalog

English

ENTRELEC Terminal Blocks Catalogue (RUS)