



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Marking Accessories



Marking Product Type: **Marker Card**

Pre-Printed Mark Details: **31 -> 40 (x10)**

Primary Product Color: **White**

Product Orientation: **Vertical**

UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Marking Product Type	Marker Card
----------------------	-------------

Configuration Features

Pre-Printed Mark Details	31 -> 40 (x10)
--------------------------	----------------

Body Features

Primary Product Color	White
Product Orientation	Vertical

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1SNA115118R1100
M6/8

Customers Also Bought

TE Part #1-1969612-8
18P FH PLUG VAL-U-LOK V0

TE Part #1SNK900653R0000
SC-JB8-3

TE Part #YDTS24Z11-02PNV001
Jam Nut: D38999, 11-02 Insert


TE Part #1969613-2
2P PM PLUG VAL-U-LOK V0

TE Part #1SNA115678R0200
M6/8.STP.RS

TE Part #1SNA163313R2400
PC8-10

TE Part #1SNA234045R2200
RC810 41->50 (X10) VERTICAL

TE Part #1SNA234047R2400
RC810 61->70 (X10) VERTICAL



TE Part #1SNA234048R0500
RC810 71->80 (X10) VERTICAL



TE Part #2238023-1
VAL-U-LOK SKT BR SN 26-22 LP

Documents

Product Drawings

RC810 31->40 (X10) VERTICAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNA234044R2100_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNA234044R2100_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNA234044R2100_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RC810 31->40 (x10) Vertical

English

ENTRELEC Terminal Block - Master Catalog

English

ENTRELEC Terminal Blocks Catalogue (RUS)