




Connectors > Terminal Blocks & Strips > Modular Terminal Blocks



Block Function: **Disconnect**
Modular Terminal Block Product Type: **Screw Clamp Terminal Block**
Rated Cross Section: **4 mm²**
Primary Product Color: **Gray**

Features

Product Type Features

Modular Terminal Block Product Type	Screw Clamp Terminal Block
-------------------------------------	----------------------------

Configuration Features

Gauge Type	A3-B3
Number of Levels	1
Number of Circuits	1
Block Function	Disconnect
Number of Positions	2

Electrical Characteristics

Impulse Withstanding Voltage Rating (IEC)	6000 V
Power Loss	.8 W
Short-Time Withstanding Current Rating @ 1s	480 A
Voltage Rating (IEC)	400 V
Operating Voltage Rating (UL & CSA) (Max) - Main Circuit	150 V
Voltage Rating (CSA)	150 V
Dielectric Test Voltage	1890 V
Current Rating (UL)	26 A
Current Rating (IEC)	26 A

Body Features

Product Weight	13.2 g[.52 oz]
----------------	----------------



Primary Product Color	Gray
-----------------------	------

Mechanical Attachment

DIN Rail Mounting Type	TH35-15, TH35-7.5
Terminal Block Disconnect Type	Blade
Connector Mounting Type	DIN Rail

Housing Features

Housing Material	Polyamide
------------------	-----------

Dimensions

Main Circuit Capacity - Twin Ferrule per Screw Clamp	24 – 16 AWG
Main Circuit Capacity - 1 Flexible Conductor per Screw Clamp	24 – 10 AWG
Main Circuit Capacity - 1 Insulated Ferrule per Screw Clamp	24 – 12 AWG
Main Circuit Capacity - 1 Non-Insulated Ferrule per Screw Clamp	.22 – 4 mm²
Main Circuit Capacity - 2 Flexible Conductors per Screw Clamp	.2 – 1.5 mm²
Main Circuit Capacity - 1 Rigid Stranded Conductor per Screw Clamp	24 – 10 AWG
Wire Stripping Length	10.5 mm[.413 in]
Main Circuit Capacity - 2 Rigid Stranded Conductors per Screw Clamp	.2 – 1.5 mm²
Tool Size	3.5 mm[.138 in]
Product Depth	51.4 mm
Product Length	51.35 mm[2.02 in]
Product Height	70.5 mm
Rated Cross Section	4 mm²
Product Spacing	6 mm[.236 in]

Usage Conditions

Storage Temperature Range	-55 – 110 °C[-67 – 230 °F]
Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-0

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK159999R0000
MC612PA



TE Part # 1SNK900001R0000
BAM4



TE Part # 1SNK900002R0000
BAZ1



TE Part # 1SNK900105R0000
ES-TC6



TE Part # 1SNK900201R0000
TC5-R1



TE Part # 1SNK900205R0000
TP4



TE Part # 1SNK900603R0000
JB85-3



TE Part # 1SNK900611R0000
UMH



TE Part # 1SNK906302R0000
JB6-2



TE Part # 1SNK906303R0000
JB6-3



TE Part # 1SNK906305R0000
JB6-5



TE Part # 1SNA113546R1400
PC6-2




TE Part # 1SNA113548R2600
PC6-10




TE Part # 1SNA116536R0500
PC6-3




TE Part # 1SNA116537R0600
PC6-4




TE Part # 1SNA164800R0300
PR3.G2




TE Part # 1SNA168500R1200
PR4



TE Part # 1SNA168700R2200
PR5



TE Part # 1SNA173220R0500
PR30



TE Part # 1SNA174300R1700
PR3.Z2


Customers Also Bought




TE Part #58063-2
HEAD (IDC) HDE-20 W/O TL



TE Part #1SNK505910R0000
ES4



TE Part #1SNK710011R0000
ZK10-3P



TE Part #1SNK710910R0000
EK10



TE Part #1SNK710911R0000
EK10-3P



TE Part #1SNK158091R0000
MC612PA PE (x100) Horizontal



TE Part #1SNK168001R0000
MC812PA + (x100) Horizontal



TE Part #1SNK168011R0000
MC812PA - (x100) Horizontal

1SNK506310R0000

Modular Terminal Blocks, Disconnect, Screw Clamp Terminal Block, 10AWG Rated
Cross Section, 4mm² Rated Cross Section, Gray



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK506310R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK506310R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK506310R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ZS4-S-R1

English

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Block - Master Catalog

English

ENTRELEC Terminal Blocks Catalogue (RUS)