6473423-1 ✔ ACTIVE


AMP | SUPERSEAL 1.0mm


TE Internal #: 6473423-1

SUPERSEAL 1.0mm, Automotive Headers, Wire-to-Board, 26 Position, 3mm [.118in] Centerline, Sealable, Horizontal, 4 Row, Black, Through Hole - Solder

View on TE.com >

Connectors > Automotive Connectors > Automotive Headers




Connector System: **Wire-to-Board**

Number of Positions: **26**

Centerline (Pitch): **3 mm [.118 in]**

Sealable: **Yes**

PCB Mount Orientation: **Horizontal**

Features

Product Type Features

Connector System	Wire-to-Board
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	26
PCB Mount Orientation	Horizontal
Number of Rows	4

Body Features

Primary Product Color	Black
Connector Code	3

Contact Features

Mating Pin Diameter	1 mm[.039 in]
Contact Mating Area Plating Material	Gold (Au)
Contact Current Rating (Max)	7 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Connector Mounting Type	Fixing Screw

Housing Features

Centerline (Pitch)	3 mm[.118 in]

Usage Conditions

Operating Temperature Range	-40 – 125 °C, -40 – 125 °C[-40 – 257 °F][-40 – 257 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-SU763-CH8172
SUPERSEAL 1.0 HOUSINGS

Also in the Series | SUPERSEAL 1.0mm



Automotive Headers(24)



Automotive Housings(11)




Automotive Seals & Cavity Plugs(1)



Automotive Terminals(6)

Customers Also Bought



TE Part #1-2176070-4
SMD Power Resistor: 2 Watt, 3521 Series



TE Part #1-172211-0
10P CAP HSG F/H EI S CONN.



TE Part #1-1625868-1
RP 2A 0.25W 301R 0.1% 25PPM 1K RL



TE Part #HD36-24-9SN
DEUTSCH HD30 HOUSINGS

TE Part #1-929504-7
TIMER, CONNECTOR HOUSING


TE Part #1011-246-0805
DEUTSCH DT BACKSHELLS

TE Part #1438156-3
GET .64 CONNECTOR SYSTEM, CONNECTOR HSG

TE Part #106455-4
FF 110 PLUG HSG 8P.



TE Part #1452737-1
COVER 113 DEGREE



TE Part #1-174928-1
070 MLC W-W CAP HSG 3P F/A

Documents

Product Drawings

SUPER SEAL 26POS CAP ASSY H AU

English

SUPER SEAL 26POS CAP ASSY H AU

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6473423-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6473423-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6473423-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

CONNECTOR SELECTOR

English

Product Specifications

Super Seal Connector

Japanese

Application Specification

Japanese

Receptacle Contact, Super Seal Connector

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

English

SUPER SEAL CONNECTOR PLUG HOUSING CONNECTOR

English

Agency Approvals

UL Report

English