



Connectors > Power Connectors > Circular Power > Circular Power Connectors > CPC SERIES 4



Connector Product Type: **Housing**
Operating Voltage: **600 VDC**
Connector System: **Wire-to-Wire**
Number of Positions: **16**
Sealable: **No**

[All CPC SERIES 4 \(8\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	16
Number of Power Positions	4
Number of Signal Positions	12

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Reverse Gender	No
Contact Type	Pin
Contact Protection	With



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Screw & Hole Thread Size	1-3/8 - 18 UNEF-2A
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Alignment	With
Mating Retention	With
Panel Mount Feature	Without
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling

Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	PA 6.6 GF
Circular Connector Shell Size	23

Dimensions

Signal Conductor Insulation Diameter	3.81 mm[.15 in]
Power Conductor Insulation Diameter	5.59 mm[.22 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Power & Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
VDE Tested	No

Packaging Features

Packaging Method	Standard
Packaging Quantity	1

Other

--	--



For Use With	Type XII Male And Multimate Pin Contact
--------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM71-C83998CC
CPC SERIES 4



TE Part # CAT-AM71-C83998P
CPC ACCESSORIES



TE Part # CAT-AM71-C83998B
CPC CABLE CLAMPS




TE Part # CAT-AM71-C83998G
CPC ACCESSORIES



TE Part # 207485-2
CPC PLUG ASSEMBLY SIZE 23-16



TE Part # 207597-1
PLUG, TYPE XII KEYING



TE Part # 207055-1
EXTENDER BACK SHELL

Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)



Circular Connector Seals(36)



Circular Power Connectors(513)



Insertion & Extraction Tools(1)



Power Contacts(5)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought



TE Part #1-2273011-1
M8 FEMALE R/A PIGTAIL



TE Part #1-1986711-4
SCREWLESS, SW,14P,5.0 PCB



TE Part #1634201-3
PRFDA1-16F-BB0CW



TE Part #1394050-2
LEAVYSEAL BACKSHELLS





TE Part #1-1564514-1
HEAVY DUTY SEALED CONNECTOR HOUSINGS



TE Part #1-66359-4
TYPE III CONTACTS STRIP



TE Part #HDC36-18-1E
DEUTSCH HD30 RECEPTACLE PROTECTIVE CAPS



TE Part #2-1904058-5
V23700C0001A408-EV-CBOX



TE Part #1-968317-3
MQS ABDECKKAPPE 24P

Documents

Product Drawings
RECEPT,SZ 23-16,CPC

English

CAD Files

3D PDF

3D

3D PDF

English

Customer View Model

ENG_CVM_207486-2_P1.2d_dxf.zip

English

Customer View Model

ENG_CVM_207486-2_P1.3d_igs.zip

English

Customer View Model

ENG_CVM_207486-2_P1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_207486-2_AL.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_207486-2_AL.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_207486-2_AL.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
AMP Circular Connectors for Commercial Signal & Power Applications
English

Product Specifications
Connector, Circular Plastic
English
Product Specification
English

Instruction Sheets
Instruction Sheet (U.S.)
English

Agency Approvals
UL Report
English