



PIDG

TE Internal #: 171507-2
PIDG, Ring Terminals & Spade Terminals, Ring Tongue, 22 – 18AWG Wire Size, .26 – 1.04mm² Wire Size, 509 – 3260CMA Wire Size, 5/16 / M8
[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**
Wire Size: **509 – 3260 CMA**
Ring & Spade Stud Size: **5/16, M8**

Features

Product Type Features

Shape Description	RING-041
Ring & Spade Stud Size	5/16, M8
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	No
Insulation Sleeve Color	Red
Stripe Color	Red
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
------------------------	-------------



Ring & Spade Terminal Orientation	Straight
-----------------------------------	----------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	8.33 mm[.328 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	27.6 mm[1.076 in]
Ring & Spade Wire Insulation Diameter (Max)	3.18 mm[.125 in]
Ring & Spade Wire Insulation Diameter	2.03 – 3.18 mm[.08 – .125 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	100
Ring & Spade Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 47386
DAHT PG PIDG 26-16 ASSY

TE Part # 58433-3
PRO CR ASSY, RBY IS9252

TE Part # 58423-1
DIE, RBY IS9252

TE Part # 47806-2
DIES PIDG 22-16 DIE SET

TE Part # 169404
CERTI-LOK DIE

Also in the Series | PIDG

Compression Connectors(17)

Crimp Terminal Housings(1)

Crimp Wire Pins, Tabs & Ferrules(41)

Knife Disconnects(11)



PCB Terminals(9)



Portable Crimp Tools(2)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(862)




Special Purpose Terminals(1)




Splices(48)

Customers Also Bought



TE Part #1-1625984-3
Power Resistors: Aluminum Housed, HSA



TE Part #1-87309-4
MOD V RECP LP



TE Part #1-1634505-0
BNC Ins Str PCB Skt 50Ohm Black




TE Part #1-5102935-6
LEVEL V ASSY DR .125CL, 20, LE




TE Part #YDTS26F11-99SNC001
Straight Plug: D38999, 11-99 Insert, Electroless Nickel Plating




TE Part #1-696423-0
TERMINAL,PIDG PVF2 R 16-14 1/2




TE Part #103349-5
20 LEVEL V COVER .125CL



TE Part #103350-5
20 LEVEL V COVER .125CL



TE Part #1-1123722-2
3.96 EP PLUG HSG 2P(NATURAL)



TE Part #1-1123722-3
3.96 EP PLUG HSG 3P(NATURAL)

Documents



Product Drawings

PIDG RING UL.CSA(22-18)

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_171507-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_171507-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_171507-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English