



TE Internal #: 1735164-1
SAS, Receptacle, Wire-to-Board, 29 Position, 1 Rows, 1 Ports,
Vertical, Through Hole - Press-Fit, 1.27mm [.049in] Centerline,
Printed Circuit Board
[View on TE.com >](#)

Connectors > PCB Connectors > SAS & MiniSAS > PT30 XFP Connectors



SAS Connector Type: **SAS**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **29**
Number of Rows: **1**

[All PT30 XFP Connectors \(17\)](#)

Features

Product Type Features

Shell	Without
SAS Connector Type	SAS
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stackable	No
Number of Positions	29
Number of Rows	1
Number of Ports	1
PCB Mount Orientation	Vertical

Contact Features



Contact Mating Area Plating Material	Gold
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	1.5 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Press-Fit
---	--------------------------

Mechanical Attachment

PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Connector Mounting Type	Board Mount

Housing Features

Housing Material	Thermoplastic
Housing Color	Black
Centerline (Pitch)	1.27 mm[.049 in]

Dimensions

Height Above PC Board	9.85 mm[.387 in]
-----------------------	------------------

Usage Conditions

High Temperature Housing	Yes
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

PCIe/SAS Generation	Gen2
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	540
Packaging Method	Box & Tray, Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-SA78-P729
SAS PLUGS

Customers Also Bought

TE Part #2053638-3
QSFP to QSFP I/O Cable Assembly: 30 AWG

TE Part #2134440-1
LGA 2011 Hardware: ILM Assembly

TE Part #6600383-5
MBXL VERT HDR 2P+16S+2P STR


TE Part #2007703-1
IMP100S,R,RA3P10C,LG,39



TE Part #2053638-5
C/A, QSFP, 5M, P1-P2, UNEQUALIZED



TE Part #2007863-1
IMP100S,H,V5P16C,RG,LEW39,4.5



TE Part #2042139-2
RA Male Connector, IEC L3



TE Part #2185223-1
ASSY, SEATING TOOL, QSFP



TE Part #2226412-1
ASSY PIN MODULE, 16-02 PCB RA, STD

Documents

Product Drawings

SAS BACKPLANE RECEPT, VERTICAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1735164-1_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1735164-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1735164-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Environmental Compliance

MD_1735164-1_121520141322_dmtec

English

MD_1735164-1_121520141322_dmtec

English

1735164-1

SAS, Receptacle, Wire-to-Board, 29 Position, 1 Rows, 1 Ports, Vertical, Through Hole - Press-Fit, 1.27mm [.049in] Centerline, Printed Circuit Board

