



TE Internal #: 5787334-1
DC Jack Connectors, Board-to-Board, 5 Position, 5mm [.197in]
Centerline, Plug, 7.2VDC Operating Voltage, Vertical, Printed
Circuit Board
[View on TE.com >](#)

Connectors > PCB Connectors > Battery Connectors & Holders > DC Jack Connectors



Connector System: **Board-to-Board**
Number of Positions: **5**
Centerline (Pitch): **5 mm [.197 in]**
Connector & Housing Type: **Plug**
Operating Voltage: **7.2 VDC**

Features

Product Type Features

Connector System	Board-to-Board
Connector & Housing Type	Plug
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	5
PCB Mount Orientation	Vertical

Electrical Characteristics

Operating Voltage	7.2 VDC
-------------------	---------

Contact Features

Contact Mating Area Plating Material Thickness	2.54 μm[100 μin]
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	7 A

Mechanical Attachment

PCB Mount Retention	Without
Connector Mounting Type	Board Mount

Housing Features

--	--



Housing Material	Polyphthalamide
Centerline (Pitch)	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-30 – 70 °C[-22 – 158 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	132
Packaging Method	Tray

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 146845-1
BATT INT,KEYLESS,5P,7.2V




TE Part # 5787446-1
HDR ASY,VERT,NO KEY,RET TAIL


Customers Also Bought



TE Part #103906-3
04 MTE HDR SRRA LATCH .100CL




TE Part #1625861-3
RH73 2A 1G 30% 500PPM



TE Part #1-770967-0
03P MINI UMNL R/A HDR ASSY SN




TE Part #1735801-1
2.0mm,Crimp,Contact



TE Part #1586040-4
4P VAL-U-LOK VRT HDR W/P V0



TE Part #9-146285-0
40 MODII HDR SRST B/A .100CL




TE Part #11030848-00
Model 44000 Series



TE Part #1419118-5
RM28802



TE Part #120957-1
UPM EXPANDED PIN ASSEMBLY



TE Part #1571625-1
TACT,6X6,SMT,J-LEAD,50GF

Documents

Product Drawings

HDR ASY,VERT,STR TAIL,7.2V

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5787334-1_O.3d_igs.zip



English

Customer View Model

[ENG_CVM_5787334-1_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_5787334-1_O.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC09_LAPTOPS_PORTABLES](#)

English

[2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English