




TE Internal #: 5787366-1  
DC Jack Connectors, Board-to-Board, 5 Position, 5mm [.197in]  
Centerline, Plug, 12VDC Operating Voltage, Right Angle, Printed  
Circuit Board  
[View on TE.com >](#)

Connectors > PCB Connectors > Battery Connectors & Holders > DC Jack Connectors



Connector System: **Board-to-Board**  
Number of Positions: **5**  
Centerline (Pitch): **5 mm [ .197 in ]**  
Connector & Housing Type: **Plug**  
Operating Voltage: **12 VDC**

Features

Product Type Features

Connector System	Board-to-Board
Connector & Housing Type	Plug
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	5
PCB Mount Orientation	Right Angle

Electrical Characteristics

Operating Voltage	12 VDC
-------------------	--------

Contact Features

Contact Mating Area Plating Material Thickness	2.54 μm[100 μin]
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	7 A

Mechanical Attachment

PCB Mount Retention	Without
Connector Mounting Type	Board Mount

Housing Features

--	--



Centerline (Pitch)	5 mm[.197 in]
--------------------	---------------

Usage Conditions

Operating Temperature Range	-30 – 70 °C[-22 – 158 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	88
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5787430-1  
HDR ASY,VERT,STR TAIL,12.0V

TE Part # 146845-1  
BATT INT,KEYLESS,5P,7.2V

Customers Also Bought

TE Part #829559-2  
MCX Connector: Male (Jack), 50 Ohm

TE Part #1612507-3  
DDR2 SO DIMM Sockets

TE Part #1-2308350-7  
CRIMP BARREL

TE Part #1982295-5  
ELCON MINI 2P RA HEADER,TRAY,W/ CODING

TE Part #5-147377-8  
100 SYS50 SMT HDRDR SHD SN

TE Part #5-445029-1  
RECEPT,36C4 RA CONN,AMPLIMITE

TE Part #1-2176366-4  
RQ 0603 590R 0.1% 10PPM 1K RL

TE Part #2-2176376-4  
RQ 0805 21K5 0.1% 10PPM 1K RL

Documents

Product Drawings  
HDR ASY,RA,RKEY,STR TAIL,12.0V  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_5787366-1\_O.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_5787366-1\_O.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_5787366-1\_O.3d\_stp.zip  
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

5787366-1

DC Jack Connectors, Board-to-Board, 5 Position, 5mm [.197in] Centerline, Plug, 12VDC Operating Voltage, Right Angle, Printed Circuit Board



Datasheets & Catalog Pages

2\_PIECE\_POWER\_CONNECTORS\_qrg\_4-1773458-1

English

Product Specifications

Product Specification

English