



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Marking Accessories



Marking Product Type: **Marker Card**

Pre-Printed Mark Details: **21 -> 30 (x10)**

Primary Product Color: **White**

Product Orientation: **Vertical**

UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

|                      |             |
|----------------------|-------------|
| Marking Product Type | Marker Card |
|----------------------|-------------|

Configuration Features

|                          |                |
|--------------------------|----------------|
| Pre-Printed Mark Details | 21 -> 30 (x10) |
|--------------------------|----------------|

Body Features

|                       |          |
|-----------------------|----------|
| Primary Product Color | White    |
| Product Orientation   | Vertical |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-2 |
|------------------------|----------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                                         |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                               |
| EU ELV Directive 2000/53/EC                   | Not Yet Reviewed                                                                                                                        |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                                 |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JUN 2020 (209)<br>SVHC > Threshold:<br>Not Yet Reviewed |



|                           |                                                                                     |
|---------------------------|-------------------------------------------------------------------------------------|
| Halogen Content           | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability                                          |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1SNA115118R1100  
M6/8

Customers Also Bought

TE Part # YDTS24Z11-02PNV001  
Jam Nut: D38999, 11-02 Insert

TE Part # 1-1755150-5  
7012AILL="RLY,STD,ON,2P,120V,60M,LLTE Part # 1SNA103588R2600  
SCFT1TE Part # 1SNA115500R2500  
M6/8.STP3TE Part # 1SNA115511R0300  
M6/12.FFTE Part # 1SNA115678R0200  
M6/8.STP.RSTE Part # 1SNA163313R2400  
PC8-10TE Part # 1SNA176675R0400  
BJMI10-2



Documents

Product Drawings

RC810 21->30 (X10) VERTICAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1SNA234043R2000\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1SNA234043R2000\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1SNA234043R2000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RC810 21->30 (x10) Vertical

English

ENTRELEC Terminal Block - Master Catalog

English

ENTRELEC Terminal Blocks Catalogue (RUS)