293651-4 ACTIVE

NECTOR

TE Internal #: 293651-4

Plug & Socket Lighting Connectors, Cable-to-Cable, 2 Position, Wire & Cable, Outlet, Contacts Preloaded, Operating Voltage 125

VAC

View on TE.com >



Connectors > Lighting Connectors > Plug & Socket Connectors



Connector System: Cable-to-Cable

Number of Positions: 2

Sealable: No

Connector & Contact Terminates To: Wire & Cable

Lighting Connector Style: Outlet

Features

Product Type Features

rioduct Type reatures	
Product Type	Connector
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Lighting Connector Style	Outlet
Configuration Features	
Keying Arrangement	LV-1
Number of Positions	2
Contacts Preloaded	Yes
Electrical Characteristics	
Operating Voltage	42 VDC
Mechanical Attachment	
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Color	White
Operation/Application	
Circuit Application	Power



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2017 (173) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Customers Also Bought














TE Part #2829724-1 CABLE ASSEMBLY, GROUND CLIP 4 INCHES



TE Part #293313-5
NECTOR S PCB CONN. ASSY STR
OUTLET







TE Part #1-293300-2 NECTOR S BUS BAR ASSY LV-2 YELLOW



TE Part #1740315-1 NECTOR S COVER FOR DISTRIBUTOR 6,7 POS

Documents

Product Drawings

CONTACT + HOUSING ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_293651-4_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_293651-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_293651-4_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

Plug & Socket Lighting Connectors, Cable-to-Cable, 2 Position, Wire & Cable, Outlet, Contacts Preloaded, Operating Voltage 125 VAC



NECTOR_S_LINE_CONNECTOR_BROCHURE

English

Agency Approvals

UL Report

English