



PIDG

TE Internal #: 32059


PIDG, Ring Terminals & Spade Terminals, Spade Tongue, 16AWG

Wire Size, 1.25 – 2mm² Wire Size, 2050 – 5180CMA Wire Size, #8 /

M4

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG SPADE TONGUE TERMINALS



Terminal & Splice Type: **Spade Tongue**

Wire Size: **2050 – 5180 CMA**

Ring & Spade Stud Size: **#8, M4**

[All PIDG SPADE TONGUE TERMINALS \(64\)](#)

Features

Product Type Features

Shape Description	SPADE-020
Ring & Spade Stud Size	#8, M4
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	No
Insulation Sleeve Color	Blue

Weight per Piece	1.105 g
Stripe Color	Blue
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Spade Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	4.17 mm[.164 in]
Tongue Thickness	.84 mm[.033 in]
Ring & Spade Overall Length	23.06 mm[.908 in]
Ring & Spade Wire Insulation Diameter (Max)	4.32 mm[.17 in]
Ring & Spade Wire Insulation Diameter	2.92 – 4.31 mm[.115 – .17 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JAN 2021
(211)
Candidate List Declared Against: JAN 2021
(211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 58433-3
PRO CR ASSY, RBY IS9252



TE Part # 59250
T-HEAD PIDG 26-14 ASSY



TE Part # 47387
DAHT PG PIDG 20-14 ASSY



TE Part # 58423-1
DIE, RBY IS9252



TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY



TE Part # 525691
DAHT PG PIDG 16-14 ASSY




TE Part # 539691-2
ERGO DIE R.B.Y




TE Part # 47387-7
DAHT PG PIDG 16-12 ASSY





TE Part # 2063030-1
SDE DIESET, RBY, UL



TE Part # 47807-1
DIES PIDG 16-14 DIE SET



TE Part # 9-1377173-7
SMP 0-0032059-0



TE Part # 169404
CERTI-LOK DIE



TE Part # 169400
CERTI-LOK

Also in the Series | PIDG



Compression Connectors(17)



Crimp Terminal Housings(1)



Crimp Wire Pins, Tabs & Ferrules(41)



Knife Disconnects(11)



PCB Terminals(9)



Portable Crimp Tools(2)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(862)



Special Purpose Terminals(1)



Splices(48)

Customers Also Bought



TE Part #1658670-5
D-Sub Connector Contacts: Pin, Brass, Signal, Size 22



TE Part #201501-1
SPIROL PIN



TE Part #1-87499-6
09 MODIV HSG COMP SR .100CL



TE Part #104482-7
16 SHORT PT RCPT HSG DR .100CL



TE Part #130527
PIDG SPADE TONGUE TERMINALS



TE Part #130560
TERMINAL SOLISTRAND RING TONGUE DIA 6,1



TE Part #YDTS26F09-35PNV001
Straight Plug: D38999, 09-35 Insert, Electroless Nickel Plating



TE Part #179544-000
D-181-2222-90/9



TE Part #1218125-5
50 POS,ASSY,PLUG,LOW PROF,109



TE Part #1218436-2
R/A RCP ASSY 15 POS SER 109

Documents

Product Drawings

TERMINAL,PIDG SPD 16-14 8

English

CAD Files

3D PDF

3D

3D PDF

English

Customer View Model

ENG_CVM_32059_C.3d_igs.zip

English

Customer View Model

ENG_CVM_32059_C.3d_stp.zip

English

Customer View Model

ENG_CVM_32059_C.2d_dxf.zip

English

Customer View Model
[ENG_CVM_CVM_32059_P.2d_dxf.zip](#)
English

Customer View Model
[ENG_CVM_CVM_32059_P.3d_igs.zip](#)
English

Customer View Model
[ENG_CVM_CVM_32059_P.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
[PIDG TERMINALS & SPLICES Quick Reference Guide](#)
English

Product Specifications
[Application Specification](#)
English

Product Environmental Compliance
[TE Material Declaration](#)
English

Agency Approvals
[UL Report](#)
English
[UL Report](#)
English