




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **52600 – 83700 CMA**

Ring & Spade Stud Size: **M6**

Features

Product Type Features

Shape Description	RING-091
Ring & Spade Stud Size	M6
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Weight per Piece	15.665 g
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Flag

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	52600 – 83700 CMA
-----------	-------------------



Stud Diameter	6.73 mm[.265 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	36.5 mm[1.437 in]
Barrel Inside Diameter	9.07 mm[.357 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	50
Ring & Spade Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1752680-5
HYP10 SOLIS FLAG 2AWG NEST

TE Part # 1752681-3
HYP10 SOLIS FLAG 6-2AWG INDENTER

TE Part # 48510
HYP8 SOLIS FLAG 2AWG NEST

Customers Also Bought

TE Part #1-770849-7
3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156

TE Part #160831-3
250 PL MKI REC. 17-13AWG TPBR

TE Part #ZPF000000000136484
NGC PLUG - FEMALE

TE Part #1-968976-9
AMP MCP, UNSEALED CONNECTOR HOUSING

TE Part #1-964298-3
TIMER, RECEPTACLE AND TAB

TE Part #1752680-5
HYP10 SOLIS FLAG 2AWG NEST

TE Part #1-2208025-1
1POS,RING TONGUE,HSG,CAP

TE Part #100284-1
2P.4MM SOCK.ASS.M27

TE Part #174931-1
070 MLC W-W CAP HSG 8P NATURAL

TE Part #164161-9
.062 PIN ASSY.3+

Documents

Product Drawings
TERMINAL,SOLIS FLAG R 2 1/4

English



CAD Files

Customer View Model

[ENG_CVM_321201_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_321201_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_321201_C.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English