




MULTI-BEAM

TE Internal #: 6450553-2
Rectangular Power Connectors, Header, Receptacle, Board-to-Board, 6 Position, 5.08mm / 7.62mm [.3in / .2in] Centerline, Printed Circuit Board

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**
Connector & Housing Type: **Receptacle**
Connector System: **Board-to-Board**
Number of Positions: **6**
Centerline (Pitch): **5.08 mm, 7.62 mm [.2 in, .3 in]**

Features

Product Type Features

Rectangular Power Connector Type	Header
Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Mating & Unmating Configuration	Sequencing
Number of Positions	6
PCB Mount Orientation	Vertical
Number of Power Positions	6
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	60 VDC, 300 VDC
-------------------	-----------------



Contact Features

Power Contact Base Material	Tin
Contact Current Rating (Max)	42 A
Contact Retention Within Housing	Without
Contact Type	Socket
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Noble Metal
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Underplate Material Thickness	3.43 µm

Termination Features

Termination Post & Tail Length	3.43 mm[.135 in]
Termination Method to Printed Circuit Board	Through Hole - Press-Fit

Mechanical Attachment

PCB Mount Retention	With
PCB Mount Retention Type	Action/Compliant Tail, Boardlock
Connector Mounting Type	Board Mount
Mating Retention Type	Action/Compliant Tail, Boardlock

Housing Features

Centerline (Pitch)	5.08 mm, 7.62 mm[.2 in][.3 in]
Housing Color	Black
Housing Material	High Temperature Thermoplastic

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	High Temperature Part - Not Glow Wire

Packaging Features

Packaging Method	Tray
------------------	------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #788153-2
CPC SERIES 1 SEALED ONE-PIECE



TE Part #1-770967-1
03P MINI UMNL R/A HDR ASSY AU



TE Part #1954289-1
Connector, Blade & Recpt 2 Pos



TE Part #1954289-2
Connector, Blade & Recpt 4 Pos



TE Part #1926736-3
MiniPAK HDL, 25s10p, RA Plug,



TE Part #1614959-8
CPF0805 1M1 0.1% 25PPM 1K RL



TE Part #2-1393210-5
PCB Power Relay: 30 Amp, Monostable DC



TE Part #1394090-1
SIGNAL HEADER



TE Part #1-640453-5
Polyester Right Angle PCB Header: 2.54mm, Unshrouded, MTA 100



TE Part #1-2333149-5
DYNAMIC 1100D REC HSG 10P X BLACK 33%GF

Documents

Product Drawings

MBXL VERT RCPT 6P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6450553-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6450553-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6450553-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



POWER_CONNECTORS_CATALOG_SEC01_BOARD_TO_BOARD

English

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English