



PIDG

TE Internal #: 2-328975-2
PIDG, Ring Terminals & Spade Terminals, Ring Tongue, 20AWG
Wire Size, .6mm² Wire Size, 1186CMA Wire Size, M12, Stud
Diameter 13.08 mm [.515 in]

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG RING TONGUE TERMINALS



Terminal & Splice Type: **Ring Tongue**
Wire Size: **1186 CMA**
Ring & Spade Stud Size: **M12**

[All PIDG RING TONGUE TERMINALS \(422\)](#)

Features

Product Type Features

Terminal Features	Sheared
Shape Description	RING-042
Ring & Spade Stud Size	M12
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Restriction

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	No
Weight per Piece	1.871 g
Stripe Color	Red
Ring & Spade Plating Material	Copper, Tin



Contact Features

Military Part Class	Class I
Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	1186 CMA
Stud Diameter	13.08 mm[.515 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	32.84 mm[1.293 in]
Ring & Spade Wire Insulation Diameter (Max)	2.79 mm[.11 in]
Ring & Spade Wire Insulation Diameter	1.17 – 2.79 mm[.046 – .11 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	Yes
----------------------	-----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



Does not contain REACH SVHC

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 59170 T-HEAD PIDG SH 26-14 ASSY	TE Part # 47386 DAHT PG PIDG 26-16 ASSY	TE Part # 47386-4 DAHT PG PIDG 26-16 ASSY	TE Part # 58433-3 PRO CR ASSY, RBY IS9252
TE Part # 58423-1 DIE, RBY IS9252	TE Part # 525690 DAHT PG PIDG 20-18 ASSY	TE Part # 2063030-1 SDE DIESET, RBY, UL	TE Part # 47806-2 DIES PIDG 22-16 DIE SET
TE Part # 59300 T-HEAD PIDG PG 26-16 ASSY	TE Part # 169404 CERTI-LOK DIE		

Also in the Series | PIDG



Compression Connectors(17)



Crimp Terminal Housings(1)



Crimp Wire Pins, Tabs & Ferrules(41)



Knife Disconnects(11)



PCB Terminals(9)



Portable Crimp Tools(2)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(862)



Special Purpose Terminals(1)



Splices(48)

Customers Also Bought




TE Part #1658543-1
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20



TE Part #123339-000
B-106-1402




TE Part #1423673-1
W51-A121B1-5=CKTBKR,THERM, ROCK



TE Part #102536-6
16 AMPMODU MT COVER DR .100CL



TE Part #1051156-1
2007 7985 00,SMA RA CABLE PLUG



TE Part #1487589-1
USB, A-B, 25/22, WHITE, 3.0M



TE Part #102394-6
16 AMP MODU MT HSG DR .100CL



TE Part #YDTS20F11-05PNV001
D38999: Square Flange, 11-05 insert



Documents

Product Drawings

TERMINAL,PIDG R IR 20 1/2

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-328975-2_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-328975-2_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-328975-2_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

CSA Certificate

English