



M12 Rail Right Angle

TE Internal #: 2350791-2

M12 Rail Right Angle, Standard Circular Connectors, Cable-to-Cable, 8 Position, Sealable, Wire & Cable, .5A Contact Current Rating (Max), Signal

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M12 R/A CRIMPED STRAIN RELIEF



Connector System: **Cable-to-Cable**

Number of Positions: **8**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **.5 A**

[All M12 R/A CRIMPED STRAIN RELIEF \(12\)](#)

Features

Product Type Features

Product Type	Connector Kit
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Full Metal Shell

Configuration Features

Number of Positions	8
Contacts Preloaded	No

Electrical Characteristics

Operating Voltage	50 VDC
-------------------	--------

Body Features

Environmental Protection	Yes
Weight	25 g[.0552 lb]
Environmental Protection Type	Elastomer Sealed
Shell Plating Material	Nickel



Shell Base Material	Brass
Circular Connector Insulation Material Type	Low Fire Hazard Thermoplastic
Hermetically Sealed	Yes

Contact Features

Contact Current Rating (Max)	.5 A
Circular Connector Contact Type	Pin

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
Polarization Code	X
Mating Alignment Type	Keyed
Mating Retention	With

Dimensions

Accepts Wire Insulation Diameter Range	8.2 mm
Wire Size	24 AWG

Usage Conditions

IP Dust Sealing Level	6
IP Water Sealing Level	7
Operating Temperature Range	-40 – 70 °C, -40 – 85 °C[-40 – 158 °F][-40 – 185 °F][-40 – 185 °F]

Operation/Application

Durability Rating	250 Cycles
Circuit Application	Signal
Shielded	Yes

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
--------------------	---

Other

Field Serviceable	Yes
-------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2297799-1
TECC0011C7



TE Part # 1-2823557-1
CRIMP TOOL FOR CRIMP FLANGE /SLEEVE




TE Part # 1-2823560-1
ASSEMBLY TOOL HANDLE FOR CRIMP FLANGE



TE Part # 1-2823561-1
UNIVERSAL INSERT (ALL M12 CODES)





TE Part # CAT-M1-M1
M12 ASSEMBLY TOOLING



TE Part # CAT-R131-IN722
CRIMP INSERT FOR USE WITH 1-2823557-1



TE Part # 601966-1
CRIMPING TOOL M22520/2-01



TE Part # CAT-ET36-M3113
12p man POE switch 1Gb



TE Part # CAT-ET36-M3113A
12p man POE switch rack



TE Part # CAT-ET36-M3113B
20p man POE switch 1Gb



TE Part # 2352900-1
8P MAN POE SWITCH 1GB 110V



TE Part # 2352905-1
24P MAN POE SWITCH 1GB 24V

Also in the Series | M12 Rail Right Angle



Standard Circular Connectors(15)


Customers Also Bought




TE Part #1838274-4
M12 Fld Ser CONN. Female Skt SlDr



TE Part #1838275-4
M12 Fld Ser CONN. Male Pin SlDr



TE Part #1-5207908-3
KIT S/R SCREW RET 90/180 DEG



TE Part #1757643-1
SMPM R/A JACK .047 S/R



TE Part #1027-017-1200
DEUTSCH DT MOUNTING CLIPS



TE Part #1060-12-0166
DEUTSCH STAMPED & FORMED CONTACTS



TE Part #2273094-1
M12 A-CODE MALE R/A PIGTAIL



TE Part #YDTS26G23-35SBV001
D38999: Straight Plug, 23-35 Insert



Documents

Product Drawings

M12 X-M-8,90,CRIMP,CAT7,TE 2297799-1

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2350791-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2350791-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2350791-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M12 X-CODED RIGHT ANGLE

English