



Connectors > Lighting Connectors > Plug & Socket Connectors



Connector System: **Cable-to-Cable**
Number of Positions: **2**
Sealable: **No**
Connector & Contact Terminates To: **Wire & Cable**
Lighting Connector Style: **Splitter**

Features

Product Type Features

Product Type	Connector
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Lighting Connector Style	Splitter

Configuration Features

Keying Arrangement	HV-3
Number of Positions	2
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	125 VAC
-------------------	---------

Contact Features

Contact Type	Pin/Socket
--------------	------------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Color	White
---------------	-------



Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

VDE Tested	No
------------	----

Packaging Features

Packaging Method	Box
------------------	-----

Other

Comment	Parallel
---------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2017 (173) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts





TE Part # 293650-1
NECTOR S T-SPLITTER STANDARD
HV-4 WHITE

Also in the Series | NECTOR S



Insertion & Extraction Tools(3)



Lighting Cable Assemblies(1)




Plug & Socket Lighting Connector
Accessories(57)




Plug & Socket Lighting Connectors(54)


Customers Also Bought




TE Part #2834049-1
LIGHT-N-LOK MODULAR LATCHED
RECEPTACLES



TE Part #2834048-1
LIGHT-N-LOK MODULAR LATCHED
PLUGS



TE Part #794955-1
VAL-U-LOK PIN BR SN 22-18AWG



TE Part #1586024-4
4P S/R FH PLUG VAL-U-LOK V2



TE Part #1586026-4
4P SR RCPT VAL-U-LOK V2



TE Part #293359-1
NECTOR S TUBE FOR SVT CABLE



TE Part #2-1676913-4
YR1 0.1% 1K91



TE Part #293387-1
NECTOR S OUTLET HV-3 WHITE



TE Part #293388-2
NECTOR S PLUG HV-3 WHITE



TE Part #2836287-1
OCEAN_2.0_Applicator-S-062F



Documents

Product Drawings

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_293650-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_293650-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_293650-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

NECTOR_S_LINE_CONNECTOR_BROCHURE

English

Agency Approvals

UL Report

English