




PIDG

TE Internal #: 326882
PIDG, Ring Terminals & Spade Terminals, Ring Tongue, 16 – 14AWG Wire Size, 1.04 – 2.62mm² Wire Size, 2050 – 5180CMA Wire Size, #6 / M3.5
[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG RING TONGUE TERMINALS



Terminal & Splice Type: **Ring Tongue**
Wire Size: **2050 – 5180 CMA**
Ring & Spade Stud Size: **#6, M3.5**

[All PIDG RING TONGUE TERMINALS \(422\)](#)

Features

Product Type Features

Shape Description	RING-041
Ring & Spade Stud Size	#6, M3.5
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	No
-----------------	----



Weight per Piece	.964 g
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	3.68 mm[.145 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	20.65 mm[.813 in]
Ring & Spade Wire Insulation Diameter (Max)	4.32 mm[.17 in]
Ring & Spade Wire Insulation Diameter	2.92 – 4.31 mm[.115 – .17 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JAN 2021
(211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58433-3
PRO CR ASSY, RBY IS9252

TE Part # 59250
T-HEAD PIDG 26-14 ASSY

TE Part # 47387
DAHT PG PIDG 20-14 ASSY

TE Part # 58423-1
DIE, RBY IS9252


TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY

TE Part # 525691
DAHT PG PIDG 16-14 ASSY


TE Part # 539691-2
ERGO DIE R.B.Y

TE Part # 47387-7
DAHT PG PIDG 16-12 ASSY






TE Part # 1-47387-0
DAHT PIDG PG 16-14 HEAD



TE Part # 2063030-1
SDE DIESET, RBY, UL



TE Part # 47807-1
DIES PIDG 16-14 DIE SET



TE Part # 169404
CERTI-LOK DIE




TE Part # 169400
CERTI-LOK

Also in the Series | PIDG




Compression Connectors(17)



Crimp Terminal Housings(1)



Crimp Wire Pins, Tabs & Ferrules(41)




Knife Disconnects(11)




PCB Terminals(9)



Portable Crimp Tools(2)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(862)




Special Purpose Terminals(1)



Splices(48)

Customers Also Bought



 TE Part #205206-8 D-Sub Crimp: Plug, Signal, 15 Posn, Pin Size 20, Shell Size 2	 TE Part #1658642-1 D-Sub Crimp: Plug, Signal, 9 Posn, Pin Size 20, Shell Size 1	 TE Part #1658643-1 D-Sub Crimp Recpt Signal 9 Posn, Socket Size 20, Shell Size 1	 TE Part #165046 PIDG FORMED WIRE PINS
 TE Part #292172-4 CT Post Header Assembly: Part. Shrouded	 TE Part #1-964296-3 TIMER, RECEPTACLE AND TAB	 TE Part #207893-1 CONTACT PIN ASSY.	 TE Part #207376-1 HSG, RECEPT 6 POSN, METRIMATE
 TE Part #19024-3 SCREW, SELF TAP, PAN HEAD	 TE Part #ZPF000000000112322 D38999/33W21R		

Documents

Product Drawings
TERMINAL,PIDG R 16-14 6

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_326882_K.3d_igs.zip
English
Customer View Model
ENG_CVM_326882_K.3d_stp.zip
English
Customer View Model
ENG_CVM_326882_K.2d_dxf.zip
English
3D PDF
English



Customer View Model

[ENG_CVM_CVM_326882_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_326882_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_326882_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[PIDG TERMINALS & SPLICES Quick Reference Guide](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_326882_07152015121_dmtec](#)

English

[MD_326882_07152015121_dmtec](#)

English

Agency Approvals

[UL Report](#)

English

[UL Report](#)

English