




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **13100 – 20800 CMA**

Ring & Spade Stud Size: **#10**

Features

Product Type Features

Shape Description	RING-091
Ring & Spade Stud Size	#10
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Weight per Piece	3.166 g
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Flag

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

--	--



Wire Size	13100 – 20800 CMA
Stud Diameter	5 mm[.197 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	23.32 mm[.918 in]
Barrel Inside Diameter	4.57 mm[.18 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	100
Ring & Spade Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1752680-8
HYP10 SOLIS FLAG 8AWG NEST

TE Part # 1752681-2
HYP10 SOLIS FLAG 8AWG INDENTER

TE Part # 48506
HYP8 SOLIS FLAG 8AWG NEST

Customers Also Bought

TE Part #2-320619-1
PIDG RING TONGUE TERMINALS

TE Part #1879074-5
Power Resistor: Aluminum Housed, 75 Watt

TE Part #1-1625995-6
Power Resistors: Aluminum Housed, HSA

TE Part #1-480305-0
03P CMNL CAP HSG F/H NATL

TE Part #1-480319-0
02P CMNL CAP HSG NATL

TE Part #2-36451-1
TERMINAL,SOLIS R 12-10 10

TE Part #104894-9
90 50/50 GRID RA HDR

TE Part #1-640250-2
3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156

TE Part #2157480-3
AMPLIMITE IP67,SZ3, 109, 25 POS,IFS, PLUG

TE Part #ZPF000000000008951
983-6SE 20-16 PN-L

Documents

Product Drawings



TERMINAL,SOLIS FLAG R 8 10

English

Agency Approvals

UL Report

English