



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**
Wire Size: **3 – 6 mm²**
Ring & Spade Stud Size: **#8, M4**
Stud Diameter: **4.3 mm [.171 in]**

Features

Product Type Features

Terminal Features	Sheared
Shape Description	RING-043
Ring & Spade Stud Size	#8, M4
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	600 V
---------------	-------

Body Features

Inspection Slot	No
Insulation Sleeve Color	Yellow
Weight per Piece	5.339 g
Stripe Color	Yellow
Ring & Spade Plating Material	Copper, Tin



Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	3 – 6 mm ²
Stud Diameter	4.3 mm[.171 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	28.03 mm[1.103 in]
Ring & Spade Wire Insulation Diameter (Max)	6.35 mm[.25 in]
Ring & Spade Wire Insulation Diameter	3.81 – 6.35 mm[.15 – .25 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	500
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58433-3
PRO CR ASSY, RBY IS9252

TE Part # 58423-1
DIE, RBY IS9252

TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY

TE Part # 59239-4
HHHT PIDG PG 12-10 ASSY

TE Part # 525692
HHHT PIDG PG 12-10 ASSY

TE Part # 169404
CERTI-LOK DIE

Customers Also Bought

TE Part #1-331456-0
TERMINAL,T-N R 4 10

TE Part #103653-5
06 MTE SHRD PIN HSG SR LATCH

TE Part #1577631-1
TERMINAL RT PIDG PEEK STRATO 18-16 AWG

TE Part #160293
PLASTI-GRIP, RING, 12-10 5MM



TE Part #130205
PIDG RING



TE Part #1-66098-9
II+ PIN, 18-16,TIN STRIP




TE Part #1-794613-0
PIN CONT 26-30 TIN PLATE L/P



TE Part #1-66399-1
III+ SKT,24-20,TIN,SMPACK



TE Part #104666-2
30 SYSTEM 50 HDR DRST SHRD



TE Part #YAFD50-12-10SNC012
RECP ASSY

Documents

Product Drawings

12-10 F.E.P.G. RING TONGUE 3BA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_342183-1_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_342183-1_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_342183-1_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance



English

Product Compliance

English