



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: Cable Clamp Kit

Cable Clamp Type: Clam Shell

Compatible With Connector Shell Size: 3

Shielded: No

Cable Insulation Diameter Range: 10.67 mm [ .42 in ]

Features

Product Type Features

|                                   |                 |
|-----------------------------------|-----------------|
| Clam Shell Length                 | Short           |
| Grommets                          | Without         |
| D-Shaped Connector Accessories    | Cable Clamp Kit |
| Connector & Contact Terminates To | Wire & Cable    |

Body Features

|                         |                     |
|-------------------------|---------------------|
| Shield Plating Material | None                |
| Cable Clamp Material    | Thermoplastic       |
| Retainer Clip Material  | Stainless Steel     |
| Color                   | Black               |
| Cable Clamp Type        | Clam Shell          |
| Cable Exit Angle        | 180° (In-Line), 45° |

Mechanical Attachment

|                          |       |
|--------------------------|-------|
| Screw & Hole Thread Size | 14702 |
|--------------------------|-------|

Dimensions

|  |  |
|--|--|
|  |  |
|--|--|



|                                 |                  |
|---------------------------------|------------------|
| Cable Insulation Diameter Range | 10.67 mm[.42 in] |
|---------------------------------|------------------|

Operation/Application

|                                      |    |
|--------------------------------------|----|
| Compatible With Connector Shell Size | 3  |
| Shielded                             | No |

Packaging Features

|                    |            |
|--------------------|------------|
| Packaging Quantity | 1          |
| Packaging Method   | Individual |

Other

|         |                                                                                                                        |
|---------|------------------------------------------------------------------------------------------------------------------------|
| Comment | All parts are packaged unassembled., Each kit is comprised of a cable clamp and male screw retainer hardware (2 each). |
|---------|------------------------------------------------------------------------------------------------------------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                 |
|-----------------------------------------------|-----------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                            |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Not Yet Reviewed |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                  |
| Solder Process Capability                     | Not applicable for solder process capability                    |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5206390-1  
AMPLIMITE ASSEMBLY,SIZE 3

Also in the Series | AMPLIMITE Kit



D-Sub Backshells & Clamps(136)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(122)

Customers Also Bought




TE Part #FC2231-0000-0100-L  
COMPRESSION LOAD CELL-100 /150MV/.5-4.5V




TE Part #1-338168-2  
D-Sub Plug Assembly: Standard, Right Angle, Shell Size 1, 2.74mm



TE Part #1-640724-0  
15P UMNL STR/REL & INSRT NATL



TE Part #1-350522-9  
09P MR STR/REL HNG BLK



TE Part #103240-5  
10 MODII HDR DRST B/A .100CL



TE Part #1-350373-9  
06P STR/REL HNGD



TE Part #1-770986-0  
MINI UMNL SOK 26-22AWG AU LP



TE Part #103957-1  
10X2 MTE RCPT SR LATCH .100CL



TE Part #1-640719-0  
02P UMNL STR/REL & INSRT NATL



TE Part #1-480634-9  
20P STR/REL HNGD BLK





Documents

Product Drawings  
CABLE CLAMP ASSEMBLY,KIT  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_1-5206478-2\_A.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_1-5206478-2\_A.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_1-5206478-2\_A.3d\_stp.zip  
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages  
AMPLIMITE Subminiature D Connectors - Cable Connectors  
English  
AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG  
English

Product Environmental Compliance  
TE Material Declaration  
English

Instruction Sheets  
Instruction Sheet (U.S.)  
English  
Instruction Sheet (U.S.)  
English