



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**
Wire Size: **2050 – 5180 CMA**
Ring & Spade Stud Size: **#8, M4**

Features

Product Type Features

Shape Description	RING-084
Ring & Spade Stud Size	#8, M4
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	2
Terminal Angle	Straight

Body Features

Weight per Piece	.776 g
Ring & Spade Plating Material	Copper, Nickel

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	2050 – 5180 CMA
-----------	-----------------



Stud Diameter	4.34 mm[.171 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	16.15 mm[.636 in]
Barrel Inside Diameter	2.16 mm[.085 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	343 °C[649 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 46447
DAHT STRATO 22-10 ASSY

TE Part # 46469
SADAHT STRATO 14 ASSY

TE Part # 8-1377172-0
SMP 0-0322694-0

Customers Also Bought

TE Part #FC2311-0000-0250-L
FORCE SENSOR ELEMENTS STOCK LIST

TE Part #1577639-1
TERMINAL RT PIDG PEEK STRATO 14-12 AWG

TE Part #1676979-3
TW 1W 1K 6.35X25PL

TE Part #1-1676979-1
TW 1W 5K 6.35X25PL

TE Part #1-1624323-0
UPW50 0.1% 5PPM 250R

TE Part #132016-1
TERMINAL PIDG RING TONGUE 20

TE Part #1622526-1
LR1 1% 5K1

TE Part #1622531-1
LR1 1% 5K6

TE Part #1986375-3
Str Plug, 3.81mm, Green, LH, 3

TE Part #1490413-2
HYP10 SOLIS HD 8AWG NEST

Documents

Product Drawings
TERMINAL,SOLIS R HR 16-14 8

English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_322694_W.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_322694_W.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_322694_W.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

STRATO-THERM Terminals & Splices for High Temperature Applications

English

Product Specifications

Product Specification

English

Product Environmental Compliance

MD_322694_031620181333_dmtec

English

MD_322694_031620181333_dmtec

English