




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **509 – 3260 CMA**

Ring & Spade Stud Size: **#6, M3.5**

Features

Product Type Features

Shape Description	RING-085
Ring & Spade Stud Size	#6, M3.5
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	No
Weight per Piece	.723 g
Ring & Spade Plating Material	Copper, Nickel

Contact Features

--	--



Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	3.68 mm[.145 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	16.38 mm[.645 in]
Ring & Spade Wire Insulation Diameter (Max)	2.8 mm[.11 in]
Ring & Spade Wire Insulation Diameter	1.3 – 2.8 mm[.051 – .11 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	343 °C[649 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

	Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46673
DAHT STRATO 22-16 ASSY



TE Part # 1213850-1
626 PNEU HD,22-16 STRATO-THERM




TE Part # 46673-1
DAHT STRATO 22-16 ASSY

Also in the Series | STRATO-THERM DIAMOND GRIP



Knife Disconnects(5)



Ring Terminals & Spade Terminals(42)



Splices(8)


Customers Also Bought




TE Part #1-321898-0
DG 22-16 HT ALUMEL R 10



TE Part #1-324227-0
PG SHUR PLUG 16-14



TE Part #1054988-1
SMA Jack-Jack Adapter 2084 8002 92



TE Part #1376766-3
SQUIB 11DIA SCR ASSY 9.3MM TYP



TE Part #1-1633730-7
CRIMPER, WIRE F .042 F



TE Part #1-1719261-0
1 POS FAKRA II PLUG HSG CODK F




TE Part #1338293-2
SHEAR, FLOATING



TE Part #1338293-4
FLOATING SHEAR



TE Part #YDIV40E23-21SNC009
RECP ASSY



TE Part #1274233-1
SPACER, RG62U, MODIFIED

Documents

Product Drawings

DG 22-16COM 22-18MIL HR R 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_323151_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_323151_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_323151_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

STRATO-THERM Terminals & Splices for High Temperature Applications

English

Product Specifications

Application Specification

English