




PIDG

TE Internal #: 323817
PIDG, Ring Terminals & Spade Terminals, Offset Ring Tongue, 16 – 14AWG Wire Size, 1.04 – 2.62mm² Wire Size, 2050 – 5180CMA Wire Size, #6

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG OFFSET RING TONGUE TERMINALS



Terminal & Splice Type: **Offset Ring Tongue**
Wire Size: **2050 – 5180 CMA**
Ring & Spade Stud Size: **#6**

All PIDG Offset Ring Tongue Terminals (7)

Features

Product Type Features

Shape Description	RING-060
Ring & Spade Stud Size	#6
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	Yes
-----------------	-----



Weight per Piece	1.137 g
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Offset Ring Tongue
Ring & Spade Terminal Orientation	Offset, Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	3.68 mm[.145 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	23.01 mm[.906 in]
Ring & Spade Wire Insulation Diameter (Max)	3.81 mm[.15 in]
Ring & Spade Wire Insulation Diameter	2.67 – 3.81 mm[.105 – .15 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JAN 2021 (211)


Does not contain REACH SVHC

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-P592-OF29
PIDG OFFSET RING TONGUE
TERMINALS

Also in the Series | PIDG

 Compression Connectors(17)	 Crimp Terminal Housings(1)	 Crimp Wire Pins, Tabs & Ferrules(41)	 Knife Disconnects(11)
---	--	---	--



PCB Terminals(9)



Portable Crimp Tools(2)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(862)



Special Purpose Terminals(1)



Splices(48)

Customers Also Bought



TE Part #110219-000
CTA-1160




TE Part #1-604771-9
CABLE TIE, 4" L, NATURAL, 100PK



TE Part #1-480698-1
02P UMNL PLUG HSG BRN




TE Part #1-480699-1
02P UMNL CAP HSG BRN



TE Part #1604896-2
ASY,RCPT,PWB MT,2 POS




TE Part #1617146-6
JMGACD-12PW = M39016/18-040P



TE Part #1-534236-4
28 MODII VRT DR CE 100/120



TE Part #YDTS26W25-61SNV001
D38999: Straight Plug, 25-61 Insert



TE Part #1056703-1
SMP Jack-Jack Adapter 2980 5004 62



TE Part #1617131-2
JMSW-12XM = M39016/11-021M

Documents



Product Drawings

TERMINAL,PIDG R OFS 16-14 6

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English