



TE Internal #: 4-2172083-2
Standard Circular Connectors, Wire-to-Board, 5 Position, Sealable,
4A Contact Current Rating (Max), Signal, Panel Mount, Reverse
Gender, Nickel, Brass
[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Board**
Number of Positions: **5**
Sealable: **Yes**
Contact Current Rating (Max): **4 A**
Circuit Application: **Signal**

Features

Product Type Features

Product Type	Connector
Connector System	Wire-to-Board
Sealable	Yes
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Number of Positions	5
Number of Power Positions	0
Number of Signal Positions	5
Contacts Preloaded	Yes

Body Features

Shell Plating Material	Nickel
Shell Base Material	Brass
Circular Connector Insulation Material Type	Polyamide



Contact Features

Contact Current Rating (Max)	4 A
Reverse Gender	Yes
Contact Layout Arrangement	Circular
Circular Connector Contact Type	Socket

Mechanical Attachment

Connector Mounting Type	Panel Mount
Polarization Code	B
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	12
-------------------------------	----

Usage Conditions

IP Water Sealing Level	8
IP Dust Sealing Level	6
Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]

Operation/Application

Circuit Application	Signal
Shielded	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C73765-M1E
M12 Field Installable Unshielded

Customers Also Bought



TE Part #1623781-2
Wirewound Resistor: Vertical Mount



TE Part #1-1623795-7
Wirewound Resistor: Horizontal Mount



TE Part #T4145415021-001
M12 Panel Mount PCB



TE Part #1558671-8
PCB Power Relay: 30 amp, Monostable DC



TE Part #1-1825027-4
FSMRA5JH04=R/A, TACT PB SW, 160G



TE Part #2-1437504-9
8080-1G1=TRANSISTOR SOCKET ASS



TE Part #1623128-1
CRG0805 1% 18K




TE Part #1-2176371-2
RQ 0603 6K04 0.1% 10PPM 5K RL





TE Part #1011-053-1205
DEUTSCH DT RETENTION SLEEVES



TE Part #1462041-8
IMB03CTS=IM RELAY 140MW 5V DIE

Documents

Product Drawings
M12.FMLE.PNLREAR.BCODE.5P.PCBSTAND.RA
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_4-2172083-2_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_4-2172083-2_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_4-2172083-2_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
M8 / M12 Connector System Catalog
English

Product Specifications
Application Specification
English