




PIDG

TE Internal #: 324015
PIDG, Ring Terminals & Spade Terminals, Spade Flange Tongue,
12 – 10AWG Wire Size, 3 – 6mm² Wire Size, 5180 – 13100CMA Wire
Size, #10

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG FLANGED SPADE TONGUE TERMINALS



Terminal & Splice Type: **Spade Flange Tongue**
Wire Size: **5180 – 13100 CMA**
Ring & Spade Stud Size: **#10**

All PIDG FLANGED SPADE TONGUE TERMINALS (52)

Features

Product Type Features

Shape Description	SPADE-024
Ring & Spade Stud Size	#10
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	No
Weight per Piece	2.447 g



Ring & Spade Plating Material	Copper, Tin
-------------------------------	-------------

Contact Features

Terminal & Splice Type	Spade Flange Tongue
Ring & Spade Terminal Orientation	Flanged, Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	5180 – 13100 CMA
Stud Diameter	4.82 mm[.19 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	25.83 mm[1.017 in]
Ring & Spade Wire Insulation Diameter (Max)	3.18 mm[.125 in]
Ring & Spade Wire Insulation Diameter	2.03 – 3.18 mm[.08 – .125 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	500
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209)



SVHC > Threshold:
Not Yet Reviewed





Halogen Content
Not Yet Reviewed for halogen content

Solder Process Capability
Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 58423-1 DIE, RBY IS9252	 TE Part # 679300-1 1210 PIDG CRIMP HEAD	 TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY
 TE Part # 59239-4 HHHT PIDG PG 12-10 ASSY	 TE Part # 539691-2 ERGO DIE R.B.Y	 TE Part # 2063030-1 SDE DIESET, RBY, UL	 TE Part # 2063361-1 DIE ASM, 12-10 PIDG, BATT TL
 TE Part # 2217330-1 KIT, BTLI, 4 TON, NA	 TE Part # 47808-6 DIES PIDG 12-10 DIE SET	 TE Part # 169404 CERTI-LOK DIE	 TE Part # 169400 CERTI-LOK





TE Part # 1-59239-4
HHHT PIDG 16-10 HEAD

Also in the Series | PIDG



Compression Connectors(17)



Crimp Terminal Housings(1)



Crimp Wire Pins, Tabs & Ferrules(41)



Knife Disconnects(11)



PCB Terminals(9)



Portable Crimp Tools(2)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(862)



Special Purpose Terminals(1)



Splices(48)

Customers Also Bought



TE Part #1676226-2
RN 0805 1K21 0.1% 10PPM 1KRL



TE Part #2-2176390-8
RQ 1206 2K21 0.1% 10PPM 5K RL




TE Part #1418762-3
MCON, RECEPTACLE AND TAB



TE Part #1452996-1
36 POS LOCK







TE Part #1633919-3
ANVIL COMBINATION



TE Part #1673600-9
CRIMPER, WIRE 'F' (.066")



TE Part #1438084-1
46 WAY WIRE SHIELD



TE Part #184153-1
2 POS. END CAP HSG., KEY C



TE Part #184171-1
2 POS. CAP HSG., KEY J



TE Part #EC6855-000
06201929-LC

Documents

Product Drawings

TERMINAL,PIDG SPD FLG 12-10 10

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_324015_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_324015_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_324015_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report



English

[UL Report](#)

English