



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **52600 – 83700 CMA**

Ring & Spade Stud Size: **3/8**

Features

Product Type Features

Shape Description	RING-044
Ring & Spade Stud Size	3/8
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	600 V
---------------	-------

Body Features

Inspection Slot	No
Insulation Sleeve Color	Red
Stripe Color	Red
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
------------------------	-------------



Ring & Spade Terminal Orientation

Offset

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	52600 – 83700 CMA
Stud Diameter	9.53 mm[.375 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	53.06 mm[2.089 in]
Ring & Spade Wire Insulation Diameter (Max)	16.05 mm[.632 in]
Ring & Spade Wire Insulation Diameter	16.05 mm[.632 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	50
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

			
TE Part # 47823 HYP8/10 TERMINYL 2AWG DIE SET	TE Part # 1490406-1 HYP10 TERMINYL 2AWG DIE SET	TE Part # 1490410-1 HYP10 PLASTI-GRIP 2AWG DIE SET	TE Part # 601129-2 HAND TOOL (A.S.I.)

Also in the Series | PLASTI-GRIP

			
Compression Connectors(3)	Crimp Wire Pins, Tabs & Ferrules(11)	Ring Terminals & Spade Terminals(208)	Splices(45)

Customers Also Bought

			
TE Part #1-747944-6 IDC D-Sub: Connector Kit, Plug, Wire to Wire, Signal, 2.77 mm	TE Part #1-747947-7 IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm	TE Part #1-1579007-6 EXTRACTION TOOL	TE Part #165171 P.G. WIRE PIN 16-14






TE Part #160294
PLASTI-GRIP, RING, 12-10 6MM



TE Part #1-745508-0
FERRULE SPLIT RING, HD



TE Part #1-968851-3
AMP MCP, RECEPTACLE AND TAB



TE Part #1604002-5
120A SGL POLE KIT, 2 AWG RED



TE Part #192004-8
BAND STRIP LA1A(.006)SIL

TE Part #YAFD50-14-18SNC012
RECP ASSY

Documents

Product Drawings

TERMINAL R PG 2 3/8

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_52044-2_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_52044-2_J.3d_igs.zip

English

Customer View Model

ENG_CVM_52044-2_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report



English

[UL Report](#)

English