




AMP Mini CT

TE Internal #: 1-353293-7

AMP Mini CT, Connector Assembly, Receptacle, Wire-to-Board, 17 Position, 1.5mm [.06in] Centerline, Insulation Displacement Crimp (IDC), 1 Row

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **17**
Centerline (Pitch): **1.5 mm [.06 in]**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	17
Number of Rows	1

Contact Features

Contact Current Rating (Max)	2 A
------------------------------	-----

Termination Features

Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)
------------------------------------	-------------------------------------

Mechanical Attachment

--	--



Mating Retention Type	Lock
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	1.5 mm[.06 in]
Housing Color	Natural

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM7053-H342
MINI COMMON TERMINATION HEADERS

TE Part # 1-292215-7
MINI CT SGL RELAY 17P NAT

TE Part # 3-353294-4
AMP MINI D/R HDR HSG 34P NATU

TE Part # 3-292216-4
MINI CT D/R RELAY 34P V NAT

TE Part # 937317-1
MIMI CT PISTOL TOOL

TE Part # 907317-1
JOINT WIRE CLAMP

Also in the Series | AMP Mini CT

PCB Connector Mounting(10)

Wire-to-Board Connector Assemblies & Housings(172)

Wire-to-Board Connector Contacts(4)

Wire-to-Board Headers & Receptacles (332)

Customers Also Bought

TE Part #1-292254-0
AMP COMMON TERMINATION HEADERS

TE Part #1-353293-9
MINI CT MT REC ASSY 19P GRAY

TE Part #1-292215-7
MINI CT SGL RELAY 17P NAT

TE Part #1-353293-8
MINI CT MT REC ASSY 18P GRAY

TE Part #1-353293-3
MINI CT MT REC ASSY 13P GRAY

TE Part #1-353293-4
MINI CT MT REC ASSY 14P GRAY

TE Part #1-292215-2
MINI CT SGL RELAY 12P NAT

TE Part #1-353293-2
MINI CT MT REC ASSY 12P GRAY



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-353293-7_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-353293-7_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-353293-7_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

6-1773454-5_AMP_Mini_CT_Connector_Series_QRG

English

Product Specifications

Product Specification

English

CT DOUBLE ROW CONNECTOR

English

Product Specification

English

Product Specification

Japanese

AMP MINI CCOMMON TERMINATION (CT), CONNECTOR, 1.5mm PITCH, M/T TYPE, LEAD FREE VERSION

Japanese

Product Environmental Compliance

MD_1-353293-7_0807201796_dmtec

English

MD_1-353293-7_0807201796_dmtec

English



Instruction Sheets

Instruction Sheet (non U.S.)

English

1.5mm Pitch Mini CT DC Drawer Connector SF Type

Japanese

Instruction Sheet (non U.S.)

Japanese

1.5mm Pitch Mini CT Hybrid Drawer Connector SF Type

Japanese

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet for Mini CT DC Drawer Connector SF Type

Japanese

1.5mm Pitch Mini CT Hybrid Drawer Connector Slim Type

Japanese

Instruction Sheet (non U.S.)

Japanese

AIR MINI PRESS FOR AMP MINI CT CONNECTOR

Japanese

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

UL

English