



PIDG

TE Internal #: 324533
PIDG, Ring Terminals & Spade Terminals, Ring Tongue, 16 – 14AWG Wire Size, 1.04 – 2.62mm² Wire Size, 2050 – 5180CMA Wire Size, #10
[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG RING TONGUE TERMINALS



Terminal & Splice Type: **Ring Tongue**
Wire Size: **2050 – 5180 CMA**
Ring & Spade Stud Size: **#10**

[All PIDG RING TONGUE TERMINALS \(422\)](#)

Features

Product Type Features

Shape Description	RING-041
Ring & Spade Stud Size	#10
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

Body Features

Inspection Slot	No
Weight per Piece	1.459 g
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
------------------------	-------------



Ring & Spade Terminal Orientation	Straight
-----------------------------------	----------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	5 mm[.197 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	27.38 mm[1.078 in]
Ring & Spade Wire Insulation Diameter (Max)	4.32 mm[.17 in]
Ring & Spade Wire Insulation Diameter	2.92 – 4.31 mm[.115 – .17 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free





Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer








This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 59250 T-HEAD PIDG 26-14 ASSY	 TE Part # 47387 DAHT PG PIDG 20-14 ASSY	 TE Part # 58423-1 DIE, RBY IS9252
 TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	 TE Part # 525691 DAHT PG PIDG 16-14 ASSY	 TE Part # 539691-2 ERGO DIE R.B.Y	 TE Part # 47387-7 DAHT PG PIDG 16-12 ASSY
 TE Part # 1-47387-0 DAHT PIDG PG 16-14 HEAD	 TE Part # 2063030-1 SDE DIESET, RBY, UL	 TE Part # 47807-1 DIES PIDG 16-14 DIE SET	 TE Part # 169404 CERTI-LOK DIE




Also in the Series | PIDG



Customers Also Bought









TE Part #2-1586019-0
20P RCPT VAL-U-LOK V0



TE Part #EF8558-000
R85049/88-15Z02



TE Part #1-350522-9
09P MR STR/REL HNG BLK



TE Part #2820163006
44A0111-18-6



TE Part #1-350523-9
15P MR STR/REL HNG BLK



TE Part #2-380937-0
MR SPLT GROMET .312 DIA BLK LF

Documents

Product Drawings

TERMINAL,PIDG R 16-14 10

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_324533_D.3d_igs.zip

English

Customer View Model

ENG_CVM_324533_D.3d_stp.zip

English

Customer View Model

ENG_CVM_324533_D.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English