



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **5180 – 13100 CMA**

Ring & Spade Stud Size: **#10**

Features

Product Type Features

Shape Description	RING-085
Ring & Spade Stud Size	#10
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	No
Weight per Piece	2.434 g
Ring & Spade Plating Material	Copper, Nickel

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Wire Size	5180 – 13100 CMA
Stud Diameter	5 mm[.197 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	26.16 mm[1.03 in]
Ring & Spade Wire Insulation Diameter (Max)	6.35 mm[.25 in]
Ring & Spade Wire Insulation Diameter	3.81 – 6.35 mm[.15 – .25 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	343 °C[649 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	500
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 59461
HHHT STRATO 12-10 ASSY

TE Part # 2217330-1
KIT, BTLI, 4 TON, NA

TE Part # 2844092-1
DIE SET, STRATO, 12-10 W

Also in the Series | STRATO-THERM DIAMOND GRIP

Knife Disconnects(5)

Ring Terminals & Spade Terminals(42)

Splices(8)

Customers Also Bought

TE Part #1-320551-3
PIDG RING TONGUE TERMINALS


TE Part #143981-000
DK-621-0434-1S

TE Part #1445692-4
ASY,PIN,QUADRAX


TE Part #1811902-1
ASY,PLUG,SIZE 19, FREE HANGING ,
N KEY



TE Part #1-1604800-4
ASSY,PLUG,QUADRAX,FREE
HANGING,12 POS



TE Part #1445693-4
BACC47GB1 - SCKT CONTACT,
QUADRAX,SZ8,RR




TE Part #127491-000
55PC1211-20-9-9CS2502



TE Part #1616055-3
A1077DD (FAA/PMA)=CONTACTOR -
S.P.S.T.



TE Part #YD369-HR33-NP00000
369 HARSH 3 WAY REC, PIN -
BACC65CR1PN



TE Part #1877626-1
Seal Assembly,Size 8 GPR

Documents

Product Drawings

DIAMOND GRIP 12-10 HR R 10

English

CAD Files

Customer View Model

ENG_CVM_325154_D.3d_igs.zip

English

Customer View Model

ENG_CVM_325154_D.3d_stp.zip

English

Customer View Model

ENG_CVM_325154_D.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

STRATO-THERM Terminals & Splices for High Temperature Applications

English

Product Specifications

Application Specification

English