



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **202 – 810 CMA**

Ring & Spade Stud Size: **#2, M2**

Features

Product Type Features

Shape Description	RING-049
Ring & Spade Stud Size	#2, M2
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	No
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

--	--

Wire Size	202 – 810 CMA
Stud Diameter	2.36 mm[.093 in]
Tongue Thickness	.46 mm[.018 in]
Ring & Spade Overall Length	11.43 mm[.45 in]
Barrel Inside Diameter	.89 mm[.035 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Box

Other

Line	Budget
------	--------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



REPRESENTATION ONLY

TE Part # 69363
DAHT STRATO SOLIS 26-20 ASSY

Also in the Series | SOLISTRAND Budget



Knife Disconnects(4)



Ring Terminals & Spade Terminals(181)



Splices(1)

Customers Also Bought




TE Part #1376020-2
DYNAMIC 2000 HDR ASSY



TE Part #1-6609987-8
CORCOM SRB SERIES IEC FILTERED INLETS



TE Part #1532211-1
M83513/01-CN, MCKS-N1-B-21PS



TE Part #1586019-4
4P RCPT VAL-U-LOK V0



TE Part #1-84981-0
1MM FFC SMT H ASSY 10P EMBOSS

TE Part #1546670-3
3P .437" DR BARRIER,W/BND SCRW

TE Part #1532188-1
M83513/02-BN, MCKS-N1-B-15SS

TE Part #1461400-4
STD OEG Miniature PCB OJ/OJE Pow Relays

TE Part #1532206-2
M83513/02-FC, MCKS-C2-B-37SS

TE Part #GA10K3CG400
CHPC-TAIWAN GOLD CHIP

Documents

Product Drawings

TERMINAL,BUDG R 26-22 2

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_33695_KU.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_33695_KU.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_33695_KU.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

MD_33695_032820181220_dmtec

English

MD_33695_032820181220_dmtec

English