




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Rectangular Tongue**

Wire Size: **5180 – 13100 CMA**

Ring & Spade Stud Size: **#8, M4**

Features

Product Type Features

Shape Description	RING-051
Ring & Spade Stud Size	#8, M4
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Ring & Spade Plating Material	Tin
-------------------------------	-----

Contact Features

Terminal & Splice Type	Rectangular Tongue
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	5180 – 13100 CMA
-----------	------------------



Stud Diameter	4.16 mm[.164 in]
Tongue Thickness	.99 mm[.039 in]
Ring & Spade Overall Length	25.2 mm[.992 in]
Barrel Inside Diameter	3.28 mm[.129 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	500
Ring & Spade Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 49935
DAHT SOLIS 22-10 ASSY



TE Part # 58546-1
PC 22-10 SOLISSPICE SPL I SHT

Customers Also Bought



TE Part #206305-1
CPC SERIES 6



TE Part #206138-8
CPC CABLE CLAMPS




TE Part #2065657-1
zd Plus, 4 pair, receptacle assy




TE Part #1393793-8
AXICOM D2N SENSITIVE



TE Part #2-353079-2
DYNAMIC 5000 HDR ASSY




TE Part #140837-2
SPLICE AMPLIVAR



TE Part #1776038-2
2P 5.08 R/A HDR,CLOSED END

TE Part #ZPF000000000146795
DMC-MD 80 B 10-01



TE Part #1-208101-1
LATCHING BLOCK KIT



TE Part #1766500-1
Assembly, Right Angle, Advance

Documents

Product Drawings
TERMINAL,SOLISTRAND 12-10 8

English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_55782-1_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_55782-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_55782-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English