



EMI Filters > Power Line Filters > Single Phase Filters > CORCOM H SERIES SINGLE PHASE FILTERS



Filter Current Rating: 10 A

Filter Mount Style: Flanged

Filter Input Termination Type: IEC

Filter Output Termination Type: .250" FASTON

Leakage Current (Max) (120VAC, 60Hz): .002 mA

[All CORCOM H SERIES SINGLE PHASE FILTERS \(15\)](#)

Features

Product Type Features

Ground Choke Option	Yes
Filter Type	Power Line
Filtering Requirements	Filtered
Filter Input Termination Type	IEC
Filter Output Termination Type	.250" FASTON

Electrical Characteristics

Voltage (Max)	250 VAC
Filter Current Rating	10 A
Leakage Current (Max) (120VAC, 60Hz)	.002 mA
Leakage Current (Max) (250VAC, 50Hz)	.005 mA

Mechanical Attachment

Filter Mount Style	Flanged
--------------------	---------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-H101
CORCOM H SERIES SINGLE PHASE FILTERS



TE Part # 1609142-1
GA400 POWER LINE CO=F6946

Also in the Series | Corcom H



Single Phase Filters(15)

Customers Also Bought



TE Part #1-66103-8
TYPE III CONTACTS LP



TE Part #1-1879417-9
CPF 0603 1M0 0.1% 25PPM 1K RL



TE Part #1622796-2
YR1 0.1% 100R




TE Part #1-206062-6
CABLE CLAMP KIT #11



TE Part #1-103958-3
8X3 MTE RCPT SR LATCH .100CL



TE Part #1-201692-9
CTR. FASTENER PLUG BLOCK-104



TE Part #1-485893-3
015 HOUSING FFC PIN 100CL SR



TE Part #1-1393130-9
PRD-7DH0-12=PRD



TE Part #NB16412001
RW-175-1/8-X-STK



TE Part #1496476-6
STD USB-A TO MINI-B ASSY, 12"

Documents

Product Drawings
10EH4C=F7437 S0

English

CAD Files
Customer View Model
ENG_CVM_6609013-6_3.3d_igs.zip

English

Customer View Model



[ENG_CVM_6609013-6_3.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_6609013-6_3.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_H_SERIES](#)

English

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

Corcom Combined Selector Charts

English