



TE Internal #: 6609053-4

Single Phase Filters, 3A Filter Current Rating, Bulkhead, IEC Input, .250" FASTON Output, Leakage Current (Max) (120VAC, 60Hz) .002 mA

[View on TE.com >](#)

EMI Filters > Power Line Filters > Single Phase Filters



Filter Current Rating: 3 A

Filter Mount Style: Bulkhead

Filter Input Termination Type: IEC

Filter Output Termination Type: .250" FASTON

Leakage Current (Max) (120VAC, 60Hz): .002 mA

Features

Product Type Features

Filter Input Termination Type	IEC
Filter Output Termination Type	.250" FASTON

Electrical Characteristics

Filter Current Rating	3 A
Leakage Current (Max) (120VAC, 60Hz)	.002 mA
Leakage Current (Max) (250VAC, 50Hz)	.005 mA

Mechanical Attachment

Filter Mount Style	Bulkhead
--------------------	----------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------




EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6609053-2
3EHT3=F7662 S0



TE Part # 6609053-3
3EHT7=F7663 S0

Customers Also Bought



TE Part #0462-209-16141
DEUTSCH SOLID CONTACTS



TE Part #1-1393122-6
KHAU-11D12-12=KH



TE Part #1-206062-6
CABLE CLAMP KIT #11




TE Part #W6P
DEUTSCH DT WEDGELOCKS





TE Part #114017-ZZ
DEUTSCH SEALING PLUGS



TE Part #1-1625999-0
Power Resistors: Aluminum Housed, HSC



TE Part #1-480698-0
02P UMNL PLUG HSG NATL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6609053-4_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6609053-4_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6609053-4_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE_HT_SERIES

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English