




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Spring Spade**

Wire Size: **202 – 810 CMA**

Ring & Spade Stud Size: **#6, M3.5**

Features

Product Type Features

Shape Description	SPADE-033
Ring & Spade Stud Size	#6, M3.5
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Inspection Slot	No
Ring & Spade Plating Material	Phosphor Bronze, Tin

Contact Features

Terminal & Splice Type	Spring Spade
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	202 – 810 CMA
-----------	---------------



Stud Diameter	3.51 mm[.138 in]
Tongue Thickness	.46 mm[.018 in]
Ring & Spade Overall Length	13.06 mm[.514 in]
Barrel Inside Diameter	1.96 mm[.077 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1
Ring & Spade Packaging Method	Loose Piece

Other

Line	Budget
------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 32863-1
TERMINAL,DG R 26-22 10

Also in the Series | SOLISTRAND Budget



Knife Disconnects(4)



Ring Terminals & Spade Terminals(181)



Splices(1)

Customers Also Bought



TE Part #326875
PIDG RING TONGUE TERMINALS



TE Part #321015
TERMINAL,PIDG R 26-22 2



TE Part #204544-2
AMPLIMITE,ASY,RCPT,FB,90,5,CONT



TE Part #2-2301994-4
RJ45 JACK INT.MAG. 1GB LED 1X1



TE Part #1888247-2
SFP Connectors




TE Part #1-1734827-3
AMP HPI 2.0MM HEADERS



TE Part #100400-8
MICRO-MATCH FSID NP



TE Part #1363301-2
5837 5031 09



Documents

Product Drawings

TERMINAL,BUDG SPR SPD 26-22 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_52734-1_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_52734-1_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_52734-1_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English