




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Spring Spade**

Wire Size: **2050 – 5180 CMA**

Ring & Spade Stud Size: **#5, M3**

Features

Product Type Features

Shape Description	SPADE-030
Ring & Spade Stud Size	#5, M3
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Ring & Spade Plating Material	Tin
-------------------------------	-----

Contact Features

Terminal & Splice Type	Spring Spade
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	3.18 mm[.125 in]
Tongue Thickness	.79 mm[.031 in]



Ring & Spade Overall Length	14.63 mm[.576 in]
Barrel Inside Diameter	2.16 mm[.085 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 53833-1
SOLIS SPR SPADE 16-14 8




TE Part # 8-320857-1
SOLIS SPD FLG 16-14, 10

Customers Also Bought



TE Part #1-1734598-5
AMP HPI 1.25MM HEADERS



TE Part #2-2176053-2
Thick Film Resistor: Current Sense



TE Part #154N-005G-RT
MEDIA ISOLATED PRESSURE STOCK LIST



TE Part #1623804-8
Wirewound Resistor: Horizontal Mount




TE Part #1546413-3
ETHERNET RJ-45 BLKHD PASSTHRU



TE Part #926307-3
6P UN-MNL AUFN-GEH



TE Part #2106751-3
Connector, Thru Hole-IDC, 3 pos, 18AWG



TE Part #2317404-3
AV19 SPM 3A FIXED RING R&B 12V



TE Part #1-747947-5
IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm



TE Part #2213189-4
Assembly, IPI Connector 26-24GA w cap

Documents

Product Drawings
SOLIS SP SPD 16-14 5
English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_53177-1_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_53177-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_53177-1_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English