



PIDG

TE Internal #: 53410-1
PIDG, Ring Terminals & Spade Terminals, Ring Tongue, 22AWG
Wire Size, .3 – 1.42mm² Wire Size, 509 – 3260CMA Wire Size, M6 / 1
/4
[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG RING TONGUE TERMINALS



Terminal & Splice Type: **Ring Tongue**
Wire Size: **509 – 3260 CMA**
Ring & Spade Stud Size: **1/4, M6**

[All PIDG RING TONGUE TERMINALS \(422\)](#)

Features

Product Type Features

Ring & Spade Stud Size	1/4, M6
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Copper
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Insulation Sleeve Color	Natural
Stripe Color	Red
Ring & Spade Plating Material	Tin-Lead

Contact Features

Military Part Class	Class I
Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment



Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	6.73 mm[.265 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	27.38 mm[1.078 in]
Ring & Spade Wire Insulation Diameter (Max)	3.18 mm[.125 in]
Ring & Spade Wire Insulation Diameter	2.03 – 3.18 mm[.08 – .125 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	150 °C[302 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	Yes
----------------------	-----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 47386 DAHT PG PIDG 26-16 ASSY	 TE Part # 47386-4 DAHT PG PIDG 26-16 ASSY	 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 59250 T-HEAD PIDG 26-14 ASSY
 TE Part # 58423-1 DIE, RBY IS9252	 TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	 TE Part # 525690 DAHT PG PIDG 20-18 ASSY	 TE Part # 539691-2 ERGO DIE R.B.Y
 TE Part # 132246-3 TERMINAL RING TONGUE PIDG 22 18	 TE Part # 2063030-1 SDE DIESET, RBY, UL	 TE Part # 47806-2 DIES PIDG 22-16 DIE SET	 TE Part # 59300 T-HEAD PIDG PG 26-16 ASSY
 TE Part # 169404 CERTI-LOK DIE	 TE Part # 169400 CERTI-LOK		

Also in the Series | PIDG



Compression Connectors(17)



Crimp Terminal Housings(1)



Crimp Wire Pins, Tabs & Ferrules(41)



Knife Disconnects(11)



PCB Terminals(9)



Portable Crimp Tools(2)



Quick Disconnects(53)



Ring Terminals & Spade Terminals(862)



Special Purpose Terminals(1)



Splices(48)


Customers Also Bought



TE Part #1-1757824-2
AMPLIMITE,ASY,RCPT,STD,90,ZN,6, CONT



TE Part #321868
TERMINAL SOLIS RING 1/0 3/8



TE Part #1-5103310-0
A/L LOW PRO HDR 50P RA BLACK




TE Part #1761607-3
IDC LOW PRO HDR 10P RA LG LAT




TE Part #33463
TERMINAL,SOLIS R 8 3/8



TE Part #321866
BODY SOLIS RING 1/0 1/4



TE Part #1-1761607-5
IDC LOW PRO HDR 50P RA LG LAT BLK




TE Part #4-1437644-7
J6-2=J6-XX JUMPER





TE Part #YDTS26W21-35SNV001
D38999: Straight Plug, 21-35 Insert



TE Part #204522-2
RECEPT ASSY,104 POSN,AMPLIMITE

Documents

Product Drawings

TERMINAL,PIDG PVF2 R 22-16 1/4

English

CAD Files

Customer View Model

ENG_CVM_53410-1_P.3d_igs.zip

English

Customer View Model

ENG_CVM_53410-1_P.3d_stp.zip

English

Customer View Model

ENG_CVM_53410-1_P.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES

English

Product Specifications

Application Specification

English