



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **20800 – 33100 CMA**

Ring & Spade Stud Size: **M10**

Features

Product Type Features

Shape Description	RING-101
Ring & Spade Stud Size	M10
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	No
Weight per Piece	4.98 g
Ring & Spade Plating Material	Copper, Tin

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------



Dimensions

Wire Size	20800 – 33100 CMA
Stud Diameter	10.5 mm[.413 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	24 mm[.945 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	400
Ring & Spade Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2015 (163) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous




materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 726344
SOL. RING TONGUE

Customers Also Bought



TE Part #163008
FF 250 TAB HSG 8P NYLON CLEAR



TE Part #163007
FF 250 REC HSG 8P NYLON CLEAR



TE Part #160860-2
FF 250 REC 0.5-1.0MM2 TPBR




TE Part #160927-2
FF 250 REC 1.0-2.5MM2 TPBR




TE Part #1473244-1
MQS, CONNECTOR HOUSING




TE Part #144617-1
TIMER, RECEPTACLE AND TAB



TE Part #1473250-1
MQS 81P LEVER(L) ASSY



TE Part #1-172469-2
PL 250 (6.3 MM) HOUSING BLUE 6/6 NYLON



TE Part #1-1633383-5
ANVIL, COMBINATION



TE Part #SRK-BS-MD-90-002
BKSHL, MED, BLK, RA, NW 22

Documents

Product Drawings
SO-RINGZUNGE D46234



English

[Datasheets & Catalog Pages](#)
[RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES](#)
English