




PIDG

TE Internal #: 53414-1
PIDG, Ring Terminals & Spade Terminals, Ring Tongue, 16AWG
Wire Size, 1.25 – 2mm² Wire Size, 2050 – 5180CMA Wire Size, M2.5
/ #4
[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > PIDG RADIATION REST/150 C RINGS/SPADES



Terminal & Splice Type: **Ring Tongue**
Wire Size: **2050 – 5180 CMA**
Ring & Spade Stud Size: **#4, M2.5**

All PIDG RADIATION REST/150 C RINGS/SPADES (41)

Features

Product Type Features

Ring & Spade Stud Size	#4, M2.5
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Copper
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Insulation Sleeve Color	Natural
Stripe Color	Blue
Ring & Spade Plating Material	Tin-Lead

Contact Features



Military Part Class	Class I
Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	3.02 mm[.119 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	17.85 mm[.703 in]
Ring & Spade Wire Insulation Diameter (Max)	3.81 mm[.15 in]
Ring & Spade Wire Insulation Diameter	2.67 – 3.81 mm[.105 – .15 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	150 °C[302 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	Yes
----------------------	-----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (13% in Component)



Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer








This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58433-3 PRO CR ASSY, RBY IS9252	TE Part # 59250 T-HEAD PIDG 26-14 ASSY	TE Part # 47387 DAHT PG PIDG 20-14 ASSY	TE Part # 58423-1 DIE, RBY IS9252
TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	TE Part # 525691 DAHT PG PIDG 16-14 ASSY	TE Part # 539691-2 ERGO DIE R.B.Y	TE Part # 47387-7 DAHT PG PIDG 16-12 ASSY
TE Part # 132246-3 TERMINAL RING TONGUE PIDG 22 18	TE Part # 2063030-1 SDE DIESET, RBY, UL	TE Part # 47807-1 DIES PIDG 16-14 DIE SET	TE Part # 169404 CERTI-LOK DIE



Also in the Series | PIDG



Customers Also Bought





TE Part #2176311-8
RP 1E 0.1W 1K37 0.1% 25PPM 1K RL

TE Part #YDTS26W09-35PNC001
D38999: Straight Plug, 09-35 Insert

TE Part #1532206-2
M83513/02-FC, MCKS-C2-B-37SS

TE Part #1058671-1
3682 2311 02

TE Part #2560-217-1231
CONT PIN

TE Part #2-2000677-0
Housing Guide Module R/A 20.3mm
Machined

Documents

Product Drawings

TERMINAL,PIDG PVF2 R 16-14 4

English

CAD Files

Customer View Model

ENG_CVM_53414-1_N1.3d_igs.zip

English

Customer View Model

ENG_CVM_53414-1_N1.3d_stp.zip

English

Customer View Model

ENG_CVM_53414-1_N1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES

English

Product Specifications

Application Specification

English